
EPIC® H-B 48 AD-LB

Housing design H-B for 2 inserts.

The robust, large panel mount base consists of the housing, a single lever, a seal and a thermoplastic cap and is suitable for investment construction applications.





Benefits
The large, robust housing for two inserts in one connector. Power and data in a single connector

Application range
Plant engineering
Plastics industry

Product features
H-A case: Wall base
Single lever
Plastic cover
Included: flat gasket

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Lever: zinc-plated steel Sealing: NBR
Protection rating:	IP 65 (latched)
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (21.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

EPIC® H-B 48 AD-LB

Prices are net prices without VAT and surcharges. Sale to business customers only.

©2023 Lapp Group - Technical changes reserved

LAPP

EPIC® H-B 48 AD-LB

PRODUCT INFORMATION

Article number	Article description	M	Pieces / PU
H-B housing: panel-mount base (cover, single lever)			
10152000	H-B 48 AD-LB	AG	1

Last Update (21.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16