FLEXIMARK® Prohibition signs

Safety signs in accordance with ISO 7010 made of laminated polyester for long-term labeling

Info
All symbols according to ISO 7010



Halogen-free

UV-resistant

Benefits
Very resistant to UV, moisture, chemicals (e.g. glass cleaner, alcohol, oil)
Scratch resistant
Powerful adhesive

Application range
Control cabinet manufacturing
Mechanical engineering
Robotics
Safety marking in industrial environment
Indoor and outdoor applications

Product features
Self-adhesive labels

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001288 ETIM 5.0 Class-Description: Labelling material
On request:	Further dimensions and symbols
Colour delivered:	red
Material:	Laminated polyester (halogen-free)
Temperature range:	-40 °C to +150 °C Processing: min. +10 °C

Last Update (23.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FLEXIMARK® Prohibition signs

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.
FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

Last Update (23.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FLEXIMARK® Prohibition signs

Article number	Article designation	Description	Dimension in mm	Markers / PU	PU
83880190	FLEXIMARK® P003 adh 25	No open flame; Fire, open ignition source and smoking prohibited	25	10	1
83880191	FLEXIMARK® P003 adh 50	No open flame; Fire, open ignition source and smoking prohibited	50	10	1
83880192	FLEXIMARK® P003 adh 100	No open flame; Fire, open ignition source and smoking prohibited	100	10	1
83880202	FLEXIMARK® P007 adh 25	No access for people with active implanted cardiac devices	25	10	1
83880203	FLEXIMARK® P007 adh 50	No access for people with active implanted cardiac devices	50	10	1
83880204	FLEXIMARK® P007 adh 100	No access for people with active implanted cardiac devices	100	10	1
83880253	FLEXIMARK® P024 adh 25	Do not walk or stand here	25	10	1
83880254	FLEXIMARK® P024 adh 50	Do not walk or stand here	50	10	1
83880255	FLEXIMARK® P024 adh 100	Do not walk or stand here	100	10	1
83880274	FLEXIMARK® P031 adh 25	Do not alter the state of the switch	25	10	1
83880275	FLEXIMARK® P031 adh 50	Do not alter the state of the switch	50	10	1
83880276	FLEXIMARK® P031 adh 100	Do not alter the state of the switch	100	10	1

Last Update (23.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FLEXIMARK® Prohibition signs



Last Update (23.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16