
SILVYN® UI 511 Insert set

SILVYN® UI Insert Set - Insert set for SILVYN® UI 511

Info
Ensuring cables do not get damaged



Reliability

Temperature-resistant

Benefits
Cable damage can be prevented

Application range
Conduit end cover
If no conduit fitting is used
In combination with protective conduit:
SILVYN® UI 511

Product features
All-round collar completely covers the protective conduit end

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000519 ETIM 5.0 Class-Description: Terminal sleeve for protective hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000519 ETIM 6.0 Class-Description: Terminal sleeve for protective hose
Material:	Nickel-plated brass
Temperature range:	-55 °C to +260 °C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (21.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SILVYN® UI 511 Insert set

Article number	Nominal size	Suitable for SILVYN® UI 511	Pieces / PU
61798091	5/16"	5/16"	10
61798096	3/8"	3/8"	10
61798097	1/2"	1/2"	10
61798092	3/4"	3/4"	5
61798093	1"	1"	5
61798094	1 1/4"	1 1/4"	2
61798090	1 1/2"	1 1/2"	2
61798095	2"	2"	2

©2023 Lapp Group - Technical changes reserved