FIPLOCK® ONE Reducer

Conduit fitting system for highest requirements, suitable for FIPLOCK® PA6 / PA12

FIPLOCK® ONE Reducer

Info
New conduit fitting system with innovative locking system



- Rail
- Good chemical resistance
- Flame-retardant
- Halogen-free
- Cold-resistant
- Maximum vibration protection
- Mechanical resistance
- Assembly time
- Low weight

Last Update (25.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FIPLOCK® ONE Reducer


Optimum strain relief


Robust


Reliability



UV-resistant


Waterproof



Benefits

Very high tensile strength due to all around tooth system
Ensures mounting safety due to integrated coding system
Excellent IP rating
Cost-saving due to quick and easy installation

Application range

Suitable for FIPLOCK® ONE-T / ONE-Y / ONE-C / ONE-CS
Suitable for FIPLOCK® PA6 / PA12
Demand of increased liquid tightness
For indoor and outdoor use

Product features

All around locking mechanism due to 360° tooth system
Locking mechanism with integrated coding system
Extended sealing range across multiple corrugated conduit waves

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Certifications:	IEC EN 61386-23 EN 45545-2 HL3
Colour delivered:	Grey (RAL 7005) Black (RAL 9005), UV-resistant
Material:	PA 6 Halogen-free Fire behaviour according to UL 94V-0
Protection rating:	IP66/IP67/IP68/IP69
Temperature range:	-45°C to +120°C

Last Update (25.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FIPLOCK® ONE Reducer

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (25.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FIPLOCK® ONE Reducer

Article number	Nominal size	Suitable for FIPLOCK® ONE-T / ONE-Y / ONE-C / ONE-CS	Suitable for FIPLOCK® PA6 / PA12	Colour	Pieces / PU
FIPLOCK® ONE-R black					
61804992	10-07	10	7	black	10
61804993	12-10	12	10	black	10
61804994	17-10	17	10	black	10
61804995	17-12	17	12	black	10
61804996	23-10	23	10	black	10
61804997	23-12	23	12	black	6
61804998	23-17	23	17	black	6
61804999	29-10	29	10	black	6
61805000	29-12	29	12	black	6
61805001	29-17	29	17	black	6
61805002	29-23	29	23	black	6
61805003	36-23	36	23	black	4
61805004	36-29	36	29	black	4
61805005	48-29	48	29	black	4
61805006	48-36	48	36	black	4
FIPLOCK® ONE-R grey					
61805007	10-07	10	7	grey	10
61805008	12-10	12	10	grey	10
61805115	17-10	17	10	grey	10
61805015	17-12	17	12	grey	10
61805016	23-10	23	10	grey	6
61805017	23-12	23	12	grey	6
61805018	23-17	23	17	grey	6
61805019	29-10	29	10	grey	6
61805020	29-12	29	12	grey	6
61805021	29-17	29	17	grey	6
61805022	29-23	29	23	grey	6
61805023	36-23	36	23	grey	4
61805024	36-29	36	29	grey	4
61805025	48-29	48	29	grey	4
61805026	48-36	48	36	grey	4

Last Update (25.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FIPLOCK® ONE Reducer



Last Update (25.12.2023)
©2023 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16