SILVYN® SNAP PET

SILVYN® SNAP PET - self-wrapping braided sleeving

Info
Simple, fast cable bundling





Assembly time

Low weight

Reliability

Temperature-resistant

Benefits
Cables can be guided in or out of the SILVYN® SNAP at any point.
Self-wrapping
Simple, fast cable bundling
Tidies away cables
Protection against dust

Application range
Easy cable protection
Bundling and guiding of cables and wires
Cable harness

Product features
Abrasion-resistant
Flexible
Self-wrapping
Cut longitudinally

Product Make-up
Polyester - PET braid sidewise rolled up

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

SILVYN® SNAP PET

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001182 ETIM 5.0 Class-Description: Braided hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001182 ETIM 6.0 Class-Description: Braided hose
On request:	Bulk containers on rolls More sizes available
Note:	Halogen and cadmium-free Fire behaviour according to UL94 V-2
Colour delivered:	Black, grey, orange, yellow, white
Material:	Polyester - PET braid sidewise rolled up
Temperature range:	-55°C to +150°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2024 Lapp Group - Technical changes reserved

LAPP

SILVYN® SNAP PET

PRODUCT INFORMATION

Article number	Nominal size	Clamping range in mm	Colour	PU (m)
SILVYN® SNAP PET				
61721280	19	19.0 - 25.0	grey	2.5
61721281	19	19.0 - 25.0	orange	2.5
61721282	19	19.0 - 25.0	black	2.5
61721283	19	19.0 - 25.0	white	2.5
61721284	19	19.0 - 25.0	yellow	2.5

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16