

EPIC® SENSOR M8Y | M12Y

Y distributor M8 | M12

Y-distributor, M12, M8, 3-pole, 4-pole, 5-pole, parallel distributor, bridged, A-coded, IP65/IP67



Supplementary automation components from Lapp



Mechanical and plant engineering



Space requirement



Waterproof

Benefits

Cost-saving due to quick and easy installation

Space-saving due to compact dimensions.

Fast and easy error tracking

Product features

Design: Plug on 2x socket

M12 design with screw hole

PWIS-free

Product Make-up

22260600:

M12, 3-pin+ PE, straight M12 plug on 2x straight M12 socket, pin 2+4 bridged

22260601:

M12, 3-pin+ PE, straight M12 plug on 2x straight M12 socket

22260602:

M12, 5-pin straight M12 plug on 2x 3-pin straight M8 socket, parallel distributor

22260603:

M8, 4-pin M8 plug on 2x 3pin M8 socket

22260604:

M8 plug on M8 socket, 3-pin parallel distributor

EPIC® SENSOR M8Y | M12Y

Technical Data

| | |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC002062 ETIM 5.0 Class-Description: Sensor-actuator adapting connector |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC002062 ETIM 6.0 Class-Description: Sensor-actuator connector |
| Material: | Contact: CuZn Contact surface: Ni/Au Knurl: Zinc die-cast, nickel-plated Gripping body: TPU, flame-retardant, self-extinguishing |
| Protection rating: | IP65/IP67 |
| Ambient temperature (operation): | Plug/socket -25°C to +90°C |
| Coding: | A-standard |
| Rated current (A): | 4 A |

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® SENSOR M8Y | M12Y

| Article number | Article designation | Rated voltage (V) | PU |
|-------------------|------------------------|-------------------|----|
| M12 Y distributor | | | |
| 22260600 | AB-C3-M12Y-2XM12FS B E | 60 | 5 |
| 22260601 | AB-C3-M12Y-2XM12FS E | 60 | 5 |
| 22260602 | AB-C5-M12Y-2XM12FS V | 60 | 5 |
| M8 Y distributor | | | |
| 22260603 | AB-C3-M8Y-2XM8FS | 30 | 5 |
| 22260604 | AB-C3-M8Y-2XM8FS V | 60 | 5 |

Last Update (25.12.2023)

©2023 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16