

EPIC® M17 Contacts

Contacts, tools, accessories for circular connectors

EPIC® M17 Contacts for the M17 circular connector series

Info

Made in Germany



Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000796

ETIM 5.0 Class-Description: Contact for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000796

ETIM 6.0 Class-Description: Contact for industrial connectors

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.



EPIC® M17 Contacts

Article number	Article description	Version	Packaging unit
0.6mm contacts, female, crimp			
44423125	M17 BCM 0,6mm 0,06-0,25	0.06-0.25mm ²	10
44423126	M17 BCM 0.6mm 0.14-0.34	0.14-0.34mm ²	10
44423127	M17 BCM 0,6mm 0,34-0,5	0.34-0.5mm ²	10
1mm contacts, female, crimp			
44423122	M17 BCM 1mm 0,06-0,25	0.06-0.25mm ²	10
44423123	M17 BCM 1mm 0.34-0.5	0.34-0.5mm ²	10
44423124	M17 BCM 1mm 0,5-1,0	0.5-1.0mm ²	10
2mm contacts, female, crimp			
44423120	M17 BCM 2mm 0,25-1,0	0.25-1.0mm ²	10
44423121	M17 BCM 2mm 1,0-2,5	1.0-2.5mm ²	10
0.6mm contacts, male, crimp			
44423133	M17 SCM 0,6mm 0,06-0,25	0.06-0.25mm ²	10
44423134	M17 SCM 0,6mm 0,14-0,34	0.14-0.34mm ²	10
44423135	M17 SCM 0,6mm 0,34-0,5	0.34-0.5mm ²	10
1mm contacts, male, crimp			
44423130	M17 SCM 1mm 0,06-0,25	0.06-0.25mm ²	10
44423131	M17 SCM 1mm 0,34-0,5	0.34-0.5mm ²	10
44423132	M17 SCM 1mm 0,5-1,0	-	10
2mm contacts, male, crimp			
44423128	M17 SCM 2mm 0,25-1,0	0.25-1.0mm ²	10
44423129	M17 SCM 2mm 1,0-2,5	1.0-2.5mm ²	10

Last Update (25.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16