

EPIC® POWER LS1 Contacts male

Contacts, tools, accessories for circular connectors

EPIC® POWER LS1 Contacts male

Info

All contacts are high quality gold plated

Contacts are designed for wide crimping range, therefore low number of variants

Made in Germany



Good chemical resistance



Wide clamping range



Corrosion-resistant



Maximum vibration protection



Mechanical resistance



Oil-resistant



Optimum strain relief



Robust



Reliability

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (20.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

**EPIC® POWER LS1 Contacts male**

Article number	Article designation	Version	For design	Pieces / PU
1mm contacts, male, crimp				
74033001	POWER LS1 A SCM 1mm AU 0.14-1.0	1 mm male 0.14 - 1.0 mm ²	LSI A1, A3, G5	10
74033000	POWER LS1 A SCM 1mm AU 0.14-1.0	1 mm male 0.14 - 1.0 mm ²	LSI A1, A3, G5	100
74034001	POWER LS1 F SCM 1mm AU 0.14-1.0	1 mm male 0.14 - 1.0 mm ²	LS1 F6, F7	10
74034000	POWER LS1 F SCM 1mm AU 0.14-1.0	1 mm male 0.14 - 1.0 mm ²	LS1 F6, F7	100
2mm contacts, male, crimp				
74033101	POWER LS1 A SCM 2mm AU 0.5-2.5	2 mm male 0.5 - 2.5 mm ²	LSI A1, A3, G5	10
74033100	POWER LS1 A SCM 2mm AU 0.5-2.5	2 mm male 0.5 - 2.5 mm ²	LSI A1, A3, G5	100
74034101	POWER LS1 F SCM 2mm AU 0.5-2.5	2 mm male 0.5 - 2.5 mm ²	LS1 F6, F7	10
74034100	POWER LS1 F SCM 2mm AU 0.5-2.5	2 mm male 0.5 - 2.5 mm ²	LS1 F6, F7	100
44420103	POWER LS1 F SCM 2mm AU 4.0	2 mm male 4.0 mm ²	LS1 F6, F7	100

Last Update (20.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16

EPIC® POWER LS1 Contacts male

