


## KMK Label holders

KMK Marking labels are cable ties with labelling area for bundling and marking cables and conduits



Halogen-free

### Benefits

Printed insert strips are placed inside the label-holder and enclosed by a dust-proof cap

### Application range

Suitable for both marking and bundling several conductors and cables in indoor areas  
For bundle diameters from 10 to 31 mm

### Product features

Labelling options: by hand or laser/ink-jet printer

### Norm references / Approvals

Smudge-proof: DIN 30646:1993-11,  
DIN VDE 0611-1:1977-11

### Included

Labels: 10 sheets with 150 (61742922) or 50 labels (61742926)  
Please order labels separately

### Product Make-up

Strap width of KMK1: 5 mm  
Bundling area of KMK1: 10-25 mm  
Strap width of KMK3: 10 mm  
Bundling area of KMK3: 16-31 mm  
Fastening loops KMK2/KMK4: 5 mm

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001288

ETIM 5.0 Class-Description: Labelling material

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001288

ETIM 6.0 Class-Description: Labelling material

Last Update (14.02.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## KMK Label holders

Colour delivered:	Transparent
Material:	Label-holder: PE, halogen-free Labels: cardboard, DIN A4 perforated, silicon free and halogen-free
Temperature range:	-40 °C to +80 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

## KMK Label holders

Article number	Article designation	Width x height (mm)	Equipment per piece	Contents (unit)
61742820	KMK 1 label-holder	29 x 8	with strap	100
61742822	KMK 2 label-holder	29 x 8	without strap	100
61742824	KMK 3 label-holder	40 x 17	with strap	50
61742826	KMK 4 label-holder	40 x 17	without strap	50
61742922	ES/LP-BW-GB labels	29 x 8	-	10
61742926	ES/KMK 3 GB labels	40 x 17	-	10

Last Update (14.02.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16