


## FLEXIMARK® Organized shrink tube FCC

FLEXIMARK® Organized shrink tubes FCC are shrink tubes for marking single cores and wires with individual text. These markers are sent with your desired text.



Mechanical and plant engineering



Rail



Flame-retardant



Halogen-free



Assembly time



Space requirement

### Benefits

Halogen-free shrink tubes with customized text

Benefit in comparison with marking rings: You do not have to mount every single character at a time, just order and mount whole series at once

Already cut to the exact length

### Application range

For single core marking

Marking before assembly

### Note

Markers will be delivered with the desired text (printing service is included in the price)

Ordering process: Customer-specific data will be emailed as an Excel file to the responsible Lapp employee when the order is made

Column A: Row 1 content

Column B: Row 2 content

Column B or C: Number of markers with corresponding text

Print jobs template: [www.lappkabel.com/service/downloadcenter/markingsystem/fleximark-customized-markings.html](http://www.lappkabel.com/service/downloadcenter/markingsystem/fleximark-customized-markings.html)

Last Update (26.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## FLEXIMARK® Organized shrink tube FCC

### Included

1 PU= 1 marker, there is no minimum purchase quantity

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001288 ETIM 5.0 Class-Description: Labelling material
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001288 ETIM 6.0 Class-Description: Labelling material
On request:	Also available as version with a 3:1 shrink ratio (not halogen-free, UL 224 approved)
Colour delivered:	Yellow
Material:	Polyolefin (halogen-free) Shrinking ratio: 2:1
Temperature range:	-30 °C to +105 °C Shrinking temperature: +90 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

# FLEXIMARK® Organized shrink tube FCC

Article number	Article designation	Colour	Shrinkage range (mm)	Length (mm)	Markers / PU
83280249	FLEXIMARK® O.shr FCC 2.4/1.2-12.5 YE	yellow	1.2 - 2.4	12.5	1
83280252	FLEXIMARK® O.shr FCC 2.4/1.2-16.6 YE	yellow	1.2 - 2.4	16.6	1
83255385	FLEXIMARK® O.shr FCC 2.4/1.2-25 YE	yellow	1.2 - 2.4	25	1
83280250	FLEXIMARK® O.shr FCC 3.2/1.6-12.5 YE	yellow	1.6 - 3.2	12.5	1
83280253	FLEXIMARK® O.shr FCC 3.2/1.6-16.6 YE	yellow	1.6 - 3.2	16.6	1
83255386	FLEXIMARK® O.shr FCC 3.2/1.6-25 YE	yellow	1.6 - 3.2	25	1
83280251	FLEXIMARK® O.shr FCC 4.8/2.4- 12.5 YE	yellow	2.4 - 4.8	12.5	1
83280254	FLEXIMARK® O.shr FCC 4.8/2.4-16.6 YE	yellow	2.4 - 4.8	16.6	1
83255387	FLEXIMARK® O.shr FCC 4.8/2.4-25 WH	white	2.4 - 4.8	25	1
83255388	FLEXIMARK® O.shr FCC 2.4/1.2-12.5 WH	white	1.2 - 2.4	12.5	1
83255389	FLEXIMARK® O.shr FCC 2.4/1.2-16.6 WH	white	1.2 - 2.4	16.6	1
83255390	FLEXIMARK® O.shr FCC 2.4/1.2-25 WH	white	1.2 - 2.4	25	1
83255391	FLEXIMARK® O.shr FCC 3.2/1.6-12.5 WH	white	1.6 - 3.2	12.5	1
83255392	FLEXIMARK® O.shr FCC 3.2/1.6-16.6 WH	white	1.6 - 3.2	16.6	1
83255393	FLEXIMARK® O.shr FCC 3.2/1.6-25 WH	white	1.6 - 3.2	25	1
83255394	FLEXIMARK® O.shr FCC 4.8/2.4-12.5 WH	white	2.4 - 4.8	12.5	1
83255395	FLEXIMARK® O.shr FCC 4.8/2.4-16.6 WH	white	2.4 - 4.8	16.6	1