



FLEXIMARK® Cablelabel PUR

FLEXIMARK® Cablelabel PUR are cable markers made of polyurethane for assembly with cable ties, particular interesting for rough areas.

Info

PUR 60x10 included in FLEXIMARK® sample bag (article no. M3251010)



Food & Beverage



Oil & Gas



Rail



Suitable for outdoor use



Good chemical resistance



Flame-retardant



Halogen-free



UV-resistant

Benefits

Good UV-resistance

Good chemical resistance

Highly flexible material

Hydrolysis and micro organism resistant

Application range

Markers could be used in any industry with a demanding environment (e.g. oil & gas, railways)

Can be mounted directly on the cable together with plastic cable ties

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® Cablelabel PUR

Norm references / Approvals

Extremely flame-retardant according to
UL 94 V0
MIL 81531 and MIL-STD-202G

Note

Can be printed with the FLEXIMARK® Software and the FLEXIMARK® Thermal transfer printer SQUIX or EOS5
Recommended ribbon:
Text colour black: FTI-Y 60-360 BK (article no. 83260201),
Text colour white: FTI-X 55-300 WH (article no. 83260260)
With customized print: see product FLEXIMARK® Cablelabel PUR FCC

Included

Delivered as a roll of labels

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001530 ETIM 5.0 Class-Description: Cable coding system
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001530 ETIM 6.0 Class-Description: Cable coding system
Colour delivered:	Standard colour: Yellow, white Also available in red, orange, blue, green and black
Material:	Halogen-free polyurethane
Temperature range:	-50°C to +100°C Could also withstand +125°C in the short term

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.
FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® Cablelabel PUR

Article number	Article designation	Colour	Width x length (mm)	Markers / PU	PU
Mounting centrally (with 1 cable tie)					
83280275	FLEXIMARK® Cablelabel PUR 20x30 YE Diamond	yellow	30.0 x 20.0	1000	1
83280276	FLEXIMARK® Cablelabel PUR 20x30 WH Diamond	white	30.0 x 20.0	1000	1
Mounting left (with 1 cable tie)					
83280277	FLEXIMARK® Cablelabel PUR 55x12 YE	yellow	12.0 x 55.0	1000	1
83280278	FLEXIMARK® Cablelabel PUR 55x12 WH	white	12.0 x 55.0	1000	1
Mounting two-sided (with 2 cable ties)					
83280279	FLEXIMARK® Cablelabel PUR 35x10 YE	yellow	10.0 x 35.0	1000	1
83260191	FLEXIMARK® Cablelabel PUR 60x10 YE	yellow	10.0 x 60.0	1000	1
83260192	FLEXIMARK® Cablelabel PUR 75x15 YE	yellow	15.0 x 75.0	1000	1
83260193	FLEXIMARK® Cablelabel PUR 75x25 YE	yellow	25.0 x 75.0	500	1
83255321	FLEXIMARK® Cablelabel PUR 100x60 YE	yellow	60.0 x 100.0	250	1
83280280	FLEXIMARK® Cablelabel PUR 35x10 WH	white	10.0 x 35.0	1000	1
83260194	FLEXIMARK® Cablelabel PUR 60x10 WH	white	10.0 x 60.0	1000	1
83260195	FLEXIMARK® Cablelabel PUR 75x15 WH	white	15.0 x 75.0	1000	1
83260196	FLEXIMARK® Cablelabel PUR 75x25 WH	white	25.0 x 75.0	500	1
83255322	FLEXIMARK® Cablelabel PUR 100x60 WH	white	60.0 x 100.0	250	1
83280260	FLEXIMARK® Cablelabel PUR 60x10 RD	red	10.0 x 60.0	1000	1
83280261	FLEXIMARK® Cablelabel PUR 75x15 RD	red	15.0 x 75.0	1000	1
83280262	FLEXIMARK® Cablelabel PUR 75x25 RD	red	25.0 x 75.0	500	1
83280263	FLEXIMARK® Cablelabel PUR 60x10 OG	orange	10.0 x 60.0	1000	1
83280264	FLEXIMARK® Cablelabel	orange	15.0 x 75.0	1000	1

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16

FLEXIMARK® Cablelabel PUR

Article number	Article designation	Colour	Width x length (mm)	Markers / PU	PU
	PUR 75x15 OG				
83280265	FLEXIMARK® Cablelabel PUR 75x25 OG	orange	25.0 x 75.0	500	1
83280266	FLEXIMARK® Cablelabel PUR 60x10 BU	blue	10.0 x 60.0	1000	1
83280267	FLEXIMARK® Cablelabel PUR 75x15 BU	blue	15.0 x 75.0	1000	1
83280268	FLEXIMARK® Cablelabel PUR 75x25 BU	blue	25.0 x 75.0	500	1
83280269	FLEXIMARK® Cablelabel PUR 60x10 BK	black	10.0 x 60.0	1000	1
83280270	FLEXIMARK® Cablelabel PUR 75x15 BK	black	15.0 x 75.0	1000	1
83280271	FLEXIMARK® Cablelabel PUR 75x25 BK	black	25.0 x 75.0	500	1
83280272	FLEXIMARK® Cablelabel PUR 60x10 GN	green	10.0 x 60.0	1000	1
83280273	FLEXIMARK® Cablelabel PUR 75x15 GN	green	15.0 x 75.0	1000	1
83280274	FLEXIMARK® Cablelabel PUR 75x25 GN	green	25.0 x 75.0	500	1

Last Update (05.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FLEXIMARK® Cablelabel PUR

