

FLEXIMARK® Flexilabel TFL

FLEXIMARK® Flexilabel TFL are blank label rolls for marking cables with character holders or for installation. Text can be printed on the labels using our marking software with a thermal transfer printer.



Good chemical resistance



Halogen-free



UV-resistant

Benefits

Suitable labels for PTE, PTEF and CAB character holders (see chapter "Character holders and accessories")
 Suitable for IP20 - IP40 Environments like public buildings such as schools, offices, hospital and malls

Application range

Installation labels
 For cable marking

Note

Easy to print via FLEXIMARK® software Flexisoft and FLEXIMARK® thermal transfer printer SQUIX, EOS5 or EOS2

Included

Delivered as a roll of labels

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001288
 ETIM 5.0 Class-Description: Labelling material

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001288
 ETIM 6.0 Class-Description: Labelling material

Colour delivered:

White or yellow
 Upon request: Yellow, green, blue, red, brown, black

Material:

Halogen-free polyester
 Polypropylene laminate

Last Update (01.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® Flexilabel TFL

Temperature range: -20°C to +80°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® Flexilabel TFL

Article number	Article designation	Colour	Width x height (mm)	Markers / PU	PU
83263023	Flexilabel TFL 9,5x17,5 WH	white	9.5 x 17.5	252	1
83263021	Flexilabel TFL 9,5x28 WH	white	9.5 x 28.0	500	1
83263019	Flexilabel TFL 9,5x35 WH	white	9.5 x 35.0	1000	1
83263025	Flexilabel TFL 9,9x66 WH	white	9.9 x 66.0	1000	1
83263032	Flexilabel TFL 12x48 WH	white	12.0 x 48.0	252	1
83263024	Flexilabel TFL 9,5x17,5 YE	yellow	9.5 x 17.5	252	1
83263022	Flexilabel TFL 9,5x28 YE	yellow	9.5 x 28.0	500	1
83263020	Flexilabel TFL 9,5x35 YE	yellow	9.5 x 35.0	1000	1
83263026	Flexilabel TFL 9,9x66 YE	yellow	9.9 x 66.0	1000	1
83263028	Flexilabel TFL 9,9x66 GN	green	9.9 x 66.0	252	1
83263029	Flexilabel TFL 9,9x66 BN	brown	9.9 x 66.0	252	1
83263030	Flexilabel TFL 9,9x66 RD	red	9.9 x 66.0	252	1
83263031	Flexilabel TFL 9,9x66 BK	black	9.9 x 66.0	252	1

Last Update (01.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16