

FLEXIMARK® Mandatory signs

Safety signs in accordance with ISO 7010 made of laminated polyester for long-term labeling

Info

All symbols according to ISO 7010



Good chemical resistance



Halogen-free



Acid-resistant



UV-resistant

Benefits

Very resistant to UV, moisture, chemicals (e.g. glass cleaner, alcohol, oil)

Scratch resistant

Powerful adhesive

Application range

Control cabinet manufacturing

Mechanical engineering

Robotics

Safety marking in industrial environment

Indoor and outdoor applications

Product features

Self-adhesive labels

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001288

ETIM 5.0 Class-Description: Labelling material

On request:

Further dimensions and symbols

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® Mandatory signs

Colour delivered:	blue
Material:	Laminated polyester (halogen-free)
Temperature range:	-40 °C to +150 °C Processing: min. +10 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® Mandatory signs

Article number	Article designation	Description	Dimension in mm	Markers / PU	PU
83880112	FLEXIMARK® M003 adh 25	Wear ear protection	25	10	1
83880113	FLEXIMARK® M003 adh 50	Wear ear protection	50	10	1
83880114	FLEXIMARK® M003 adh 100	Wear ear protection	100	10	1
83880115	FLEXIMARK® M004 adh 25	Wear eye protection	25	10	1
83880116	FLEXIMARK® M004 adh 50	Wear eye protection	50	10	1
83880117	FLEXIMARK® M004 adh 100	Wear eye protection	100	10	1
83880127	FLEXIMARK® M008 adh 25	Wear safety footwear	25	10	1
83880128	FLEXIMARK® M008 adh 50	Wear safety footwear	50	10	1
83880129	FLEXIMARK® M008 adh 100	Wear safety footwear	100	10	1
83880130	FLEXIMARK® M009 adh 25	Wear protective gloves	25	10	1
83880131	FLEXIMARK® M009 adh 50	Wear protective gloves	50	10	1
83880132	FLEXIMARK® M009 adh 100	Wear protective gloves	100	10	1

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FLEXIMARK® Mandatory signs

