

FLEXIMARK® TA Foam Panel strip

FLEXIMARK® Labels are markers made of polyester foam and are an inexpensive alternative for engraved plastic markers for component marking in the electrical industry (e.g. marking cabinets).



Mechanical and plant engineering



Good chemical resistance



Halogen-free



Assembly time



UV-resistant

Benefits

Good UV-resistance

Self-adhesive on many surfaces

Cost-efficient alternative to traditionally used engraved plastic signs

Application range

Identification of electrical components, panels, push buttons and information signs

Note

Easy to print via FLEXIMARK® software Flexisoft and FLEXIMARK® thermal transfer printer SQUIX, EOS5 or EOS2

Recommended ribbon: FTI-Y 60-360 BK (article no. 83260201)

Included

Delivered as a roll of labels

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001288

ETIM 5.0 Class-Description: Labelling material

Adhesive:

Acrylic-based permanent adhesive

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® TA Foam Panel strip

Colour delivered:	Silver White in web catalogue
Material:	Polyester foam
Temperature range:	-40 °C to +90 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® TA Foam Panel strip

Article number	Article designation	Colour	Width (mm)	m / PU	PU
Panel strip					
83255355	FLEXIMARK® TA foam 13-20m SR	silver	13	20	1
83255356	FLEXIMARK® TA foam 15-20m SR	silver	15	20	1
83255357	FLEXIMARK® TA foam 18-20m SR	silver	18	20	1
83255358	FLEXIMARK® TA foam 25-20m SR	silver	25	20	1
83255359	FLEXIMARK® TA foam 30-20m SR	silver	30	20	1
83255360	FLEXIMARK® TA foam 35-20m SR	silver	35	20	1
83255361	FLEXIMARK® TA foam 50-20m SR	silver	50	20	1
83255362	FLEXIMARK® TA foam 80-20m SR	silver	80	20	1
83255363	FLEXIMARK® TA foam 100-20m SR	silver	100	20	1