

FLEXIMARK® TA Labels Component marking

TA labels are self-adhesive labels for marking cabinets and other components in the electrical industry. Can be printed with thermal transfer printers

Info

Sample labels are available upon request



Mechanical and plant engineering



Good chemical resistance



Halogen-free



Assembly time



UV-resistant

Benefits

Good UV resistance

Smudge and scratch resistant and resistant to oils and chemicals as well

Application range

Identification of electrical components, panels, push buttons and information signs

Note

Easy to print via FLEXIMARK® software Flexisoft and FLEXIMARK® thermal transfer printer SQUIX, EOS5 or EOS2

Recommended ribbon: R71 110-360 resin BK (article no. 83259609)

More sizes and colours available on request

Included

Delivered as a roll of labels

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

FLEXIMARK® TA Labels Component marking

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001288 ETIM 5.0 Class-Description: Labelling material
Adhesive:	Acrylic-based permanent adhesion Bonding strength: 15 N/mm
Colour delivered:	Yellow, white Silver on demand
Material:	Halogen-free polyester
Temperature range:	-40 °C to +150 °C Processing: min. +10 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.
FLEXIMARK® products are sold in packaging units. As example if you like to order 640 labels of LCK 32 you just need to order 1 PU instead of 640 single labels.

FLEXIMARK® TA Labels Component marking

Article number	Article designation	Colour	Width x height (mm)	Markers / PU	PU
83259611	FLEXIMARK® TA label 15-6 YE	yellow	15.6 x 6.0	10000	1
83259628	FLEXIMARK® TA label 18-9 YE	yellow	18.0 x 9.0	10000	1
83259634	FLEXIMARK® TA label 20-8 YE	yellow	20.0 x 8.0	10000	1
83259641	FLEXIMARK® TA label 25.4-12.7 YE	yellow	25.4 x 12.7	10000	1
83259653	FLEXIMARK® TA label 26-10 YE	yellow	26.0 x 10.0	10000	1
83259664	FLEXIMARK® TA label 26.5-17.5 YE	yellow	26.5 x 17.5	5000	1
83259683	FLEXIMARK® TA label 32-9.5 YE	yellow	32.0 x 9.5	10000	1
83259594	FLEXIMARK® TA label 37-9 YE	yellow	37.0 x 9.0	2000	1
83259574	FLEXIMARK® TA label 38-13 YE	yellow	38.0 x 13.0	5000	1
83259694	FLEXIMARK® TA label 38-19 YE	yellow	38.0 x 19.0	2000	1
83259700	FLEXIMARK® TA label 45-23 YE	yellow	45.0 x 23.0	2000	1
83259706	FLEXIMARK® TA label 47-28 YE	yellow	47.0 x 28.0	1500	1
83259712	FLEXIMARK® TA label 50-23 YE	yellow	50.0 x 23.0	2000	1
83259718	FLEXIMARK® TA label 60-36 YE	yellow	60.0 x 36.0	1000	1
83259724	FLEXIMARK® TA label 65-35 YE	yellow	65.0 x 35.0	1000	1
83259736	FLEXIMARK® TA label 70-48 YE	yellow	70.0 x 48.0	1000	1
83259783	FLEXIMARK® TA label 75-28 YE	yellow	75.0 x 28.0	2000	1
83259755	FLEXIMARK® TA label 101.6-23 YE	yellow	101.6 x 23.0	2000	1
83259763	FLEXIMARK® TA label 101.6-36 YE	yellow	101.6 x 36.0	1000	1
83259610	FLEXIMARK® TA label 15-6 WH	white	15.0 x 6.0	10000	1
83259629	FLEXIMARK® TA label 18-9	white	18.0 x 9.0	10000	1

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16

FLEXIMARK® TA Labels Component marking

Article number	Article designation	Colour	Width x height (mm)	Markers / PU	PU
	WH				
83259635	FLEXIMARK® TA label 20-8 WH	white	20.0 x 8.0	10000	1
83259643	FLEXIMARK® TA label 25.4-12.7 WH	white	25.4 x 12.7	10000	1
83259655	FLEXIMARK® TA label 26-10 WH	white	26.0 x 10.0	10000	1
83259665	FLEXIMARK® TA label 26.5-17.5 WH	white	26.5 x 17.5	5000	1
83259685	FLEXIMARK® TA label 32-9.5 WH	white	32.0 x 9.5	10000	1
83259593	FLEXIMARK® TA label 37-9 WH	white	37.0 x 9.0	2000	1
83259573	FLEXIMARK® TA label 38-13 WH	white	38.0 x 13.0	5000	1
83259695	FLEXIMARK® TA label 38-19 WH	white	38.0 x 19.0	2000	1
83259701	FLEXIMARK® TA label 45-23 WH	white	45.0 x 23.0	2000	1
83259707	FLEXIMARK® TA label 47-28 WH	white	47.0 x 28.0	1500	1
83259713	FLEXIMARK® TA label 50-23 WH	white	50.0 x 23.0	2000	1
83259719	FLEXIMARK® TA label 60-36 WH	white	60.0 x 36.0	1000	1
83259725	FLEXIMARK® TA label 65-35 WH	white	65.0 x 35.0	1000	1
83259737	FLEXIMARK® TA label 70-48 WH	white	70.0 x 48.0	1000	1
83259782	FLEXIMARK® TA label 75-28 WH	white	75.0 x 28.0	2000	1
83259756	FLEXIMARK® TA label 101.6-23 WH	white	101.6 x 23.0	2000	1
83259764	FLEXIMARK® TA label 101.6-36 WH	white	101.6 x 36.0	1000	1
83259673	FLEXIMARK® TA label 30-20 WH	white	30.0 x 20.0	6000	1

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16