FLEXIMARK® Stainless steel kit

FLEXIMARK® Stainless Steel Kit is a box with all you need for marking on-site in demanding environments as acid-proved holders and embossed character strips for marking in demanding environments





- Mechanical and plant engineering
- Oil & Gas
- Rail
- Suitable for outdoor use
- Good chemical resistance
- Corrosion-resistant
- Oil-resistant
- Acid-resistant
- Temperature-resistant
- UV-resistant

Benefits

The basic equipment of the FLEXIMARK® stainless steel system in a handy box

Application range

Cable and component marking system
Quick and easy on-site assembly

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

FLEXIMARK® Stainless steel kit

Markers could be used in any industry with a demanding environment (e.g. oil & gas, railways)

Norm references / Approvals
Achilles JQS certified

Note
Single parts included in the box could be purchased separately (e.g. special pliers= article no. 61790180)

Included
Characters A-Ö / 0-9: 40 pcs.
Special characters +-/:.ü and symbol for earthing: 40 pcs.
Blank characters: 40 pcs.
Character holders (each 5 with boreholes and 5 with fastening loops for cable ties) with lengths of 286, 109, 83.1, 60.4, and 48.8 mm
Steel cable ties LS 4.6x200: 10 pcs.

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001288 ETIM 5.0 Class-Description: Labelling material
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001288 ETIM 6.0 Class-Description: Labelling material
Dimensions:	Character strips: 9.5 x 6 x 0.75 mm Box: 440 x 380 x 100 mm
Material:	Acid resistant stainless steel EN 1.4404 (SS2348, AISI 316L)
Temperature range:	-80 °C to +500 °C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.
Please request our data sheet for further clarification on the different types of kits.

©2024 Lapp Group - Technical changes reserved

LAPP

PRODUCT INFORMATION

FLEXIMARK® Stainless steel kit

Article number	Article designation	Version	PU
83254222	FLEXIMARK® Kit Stainless Steel without pliers	without pliers	1
83254223	FLEXIMARK® Kit Stainless Steel with special pliers	with special pliers for´preventing the signs falling off	1
83254224	FLEXIMARK® Kit Stainless Steel with cable tie pliers	With cable tie pliers	1

Last Update (22.02.2024)
©2024 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16