

SILVYN® FPAG 90° PG

SILVYN® FPAG 90° PG - conduit fitting for SILVYN® FPAS



-  Halogen-free
-  Maximum vibration protection
-  Assembly time
-  Optimum strain relief
-  Space requirement
-  Temperature-resistant
-  Variety of approval certifications

Benefits

90° elbow allows easy installation
Fast assembly
High-tensile
Sealing
Vibration protection

Application range

In combination with protective conduit:
SILVYN® FPAS
Applications with strong vibrations

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® FPAG 90° PG

Product features

In black colour UV-resistant and weather-proofed
Removeable with a screwdriver

Norm references / Approvals

UL FILENUMBER E308201

Product Make-up

PG connection thread
90° elbow
Body
Upper part with integrated all-round toothing

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001176 ETIM 5.0 Class-Description: Screw connection for corrugated plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001176 ETIM 6.0 Class-Description: Screw connection for corrugated plastic hose
Certifications:	IEC EN 61386-23
Colour delivered:	Grey (RAL 7031) Black (RAL 9005), UV-resistant
Material:	PA66 Halogen-free
Protection rating:	IP 66
Temperature range:	-50°C to +135°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® FPAG 90° PG

Article number	Suitable for SILVYN® FPAS	Pieces / PU
SILVYN® FPAG 90° PG black		
55506715	10	10
55506725	13	10
55506735	16	10
55506745	16	10
55506755	18	10
55506815	21	10
55506765	21	10
55506775	28	10
55506785	34	10
55506795	42	1
55506805	54	1
55506825	67	1
SILVYN® FPAG 90° PG grey		
55506710	10	10
55506720	13	10
55506730	16	10
55506740	16	10
55506750	18	10
55506810	21	10
55506760	21	10
55506770	28	10
55506780	34	10
55506790	42	1
55506800	54	1
55506820	67	1

Last Update (27.04.2024)

©2024 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16