

POF Connector F-SMA and ST(BFOC)

Accessories for polymer optical fibre cables, connector type FSMA and ST(BFOC)

POF Connector F-SMA and ST(BFOC) for different cable types and dimensions, for crimping or clamping

Info

FSMA and ST(BFOC) connectors for POF cable assembly



Benefits

As crimp or clamp version for easy assembling

Product features

FSMA and ST(BFOC) connector
with knurled nut or
hexagonal nut for crimping,
gluing or easy clamping
Suitable for 2.2 mm POF
Available for different cable diameters
(2.2 mm and 6.0 mm)
Connector including bend protection boot and dust cap
bend protection boot colour:
black and red

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001122

ETIM 5.0 Class-Description: Fibre optic connector

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001122

ETIM 6.0 Class-Description: Fibre optic connector

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

POF Connector F-SMA and ST(BFOC)

Article number	Article designation
FSMA Connectors with knurled nut for crimping	
29135099	POF Connector FSMA Crimp 2.2 /4PC
29135098	POF Connector FSMA Crimp 2.2 /50PC
29137099	POF Connector FSMA Crimp 6.0 /4PC
29137098	POF Connector FSMA Crimp 6.0 /50PC
FSMA Connectors with hexagonal nut for crimping	
29135089	POF Connector FSMA Hex Crimp 2.2 /4PC
29135088	POF Connector FSMA Hex Crimp 2.2 /50PC
29132089	POF Connector FSMA Hex Crimp 6.0 /4PC
29132088	POF Connector FSMA Hex Crimp 6.0 /50PC
FSMA Connectors with knurled nut for clamping	
29130099	POF Connector FSMA Clamp 2.2 /4PC
29130098	POF Connector FSMA Clamp 2.2 /50PC
FSMA Connectors with hexagonal nut for clamping	
29130089	POF Connector FSMA Hex Clamp 2.2 /4PC
29130088	POF Connector FSMA Hex Clamp 2.2 /50PC
ST(BFOC) Connectors for crimping	
29125099	POF Connector ST(BFOC) Crimp 2.2 /4PC
29125098	POF Connector ST(BFOC) Crimp 2.2 /50PC
ST(BFOC) Connectors for clamping	
29120099	POF Connector ST(BFOC) Clamp 2.2 /4PC
29120098	POF Connector ST(BFOC) Clamp 2.2 /50PC

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16