



SILVYN® SP-PU


SILVYN® SP-PU - black PUR conduit



SILVYN® SSV/SSV-M + SCH
IP 54



SILVYN® SSVZ/SSVZ-M + SCH
IP 54



SILVYN® USK/USK-M
IP 54



SILVYN® SCH



Good chemical resistance



Mechanical resistance



UV-resistant



Waterproof

Benefits

Protection against mechanical stress
Abrasion protection
Protection against chemicals
UV-resistant and weather-resistant

Application range

Cable protection
Bundling and guiding of cables and wires
Outdoors
In harsh environment

Product features

Tear-resistant
Oil and petrol-resistant
Halogen-free
Resistant to microbes
Dimensionally stable

Last Update (18.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® SP-PU

Product Make-up

Hard PVC inner spiral
Polyurethane outer sheath

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001177 ETIM 5.0 Class-Description: Protective plastic hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001177 ETIM 6.0 Class-Description: Protective plastic hose
Certifications:	IEC EN 61386-23
Colour delivered:	Black (RAL 9005), UV-resistant
Material:	PUR with hard PVC spiral Fire behaviour according to UL 94V-0
Temperature range:	-20°C to +90°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® SP-PU

Article number	ID x OD mm	Bending radius (mm)	Suitable for SILVYN® SSV-M/SSVZ-M	Suitable for SILVYN® USK-M	Suitable for SILVYN® SSV/SSVZ	Suitable for SILVYN® USK	Suitable for SILVYN® SCH	PU ring (m)
SILVYN® SP-PU								
61793620	10.0 x 14.0	50	16 x 1,5/1	12 x 1,5	9/1	9	10 - 16 S	25
61793630	12.0 x 16.0	60	16 x 1,5/2	16 x 1,5	9/2	11	12 - 20 S	25
61793640	14.0 x 18.0	70	20 x 1,5/1	-	11/1	13,5	12 - 20 S	25
61793650	16.0 x 20.0	80	20 x 1,5/2	20 x 1,5	11/2	16	16 - 25 S	25
61793660	22.0 x 27.0	110	25 x 1,5	25 x 1,5	-	21	20 - 32 S	25
61793670	30.0 x 36.0	150	32 x 1,5	32 x 1,5	29/1	29	25 - 40 S	25
61793680	38.0 x 44.0	200	40 x 1,5	40 x 1,5	36	36	32 - 50 S	25

Last Update (18.09.2020)

©2020 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03.16