

## Cable trolley system I-beam

Lapp Group offers a complete cable trolley system both for flat cables and for round cables.

### Info

Mounting space-saving, since no side offset to the beam



### Benefits

Gentle cable clamps prevent the cables from sharp bends

### Application range

Crane and conveying machinery  
For hoisting equipment and conveyor systems  
Mechanical engineering  
Not suitable for applications in explosive environments

### Note

Round- and flat cables are not allowed to be combined side by side or below each other  
Don't assemble more than three clamps for round cables below each other  
Bending radius on the bracket corresponds to a fixed installation

### Product Make-up

The installation of a system depends on various criteria, e.g. maximum cable slack (cable weight) and working length.

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002935 ETIM 5.0 Class-Description: Accessories for cable carrying system
General:	Max. cable load: 20 kg
Material:	Metal parts: Galvanized steel Clamps: Polyamide 6
Temperature range:	-40 °C to +120 °C

### Note

CIBES® is a registered trade mark of INOMEK AB  
Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## Cable trolley system I-beam

Prices are net prices without VAT and surcharges. Sale to business customers only.

## Cable trolley system I-beam

Article number	Article designation	Max. flat cable dimensions mm	max. round cable diameter mm	Pieces / PU
62200473	Cable clamp flat I-Beam	15.0 x 54.0	-	1
62200474	Cable clamp flat I-Beam b	15.0 x 54.0	-	1
62200490	End clamp flat I-Beam	15.0 x 54.0	-	1
62200491	End clamp flat I-Beam b	15.0 x 54.0	-	1
62200451	End clamp round I-Beam	-	-	-
62200452	Cable trolley I-Beam 2 wheels	-	-	-
62200472	Cable trolley I-Beam 4 wheels	-	-	1
62200437	Clamp round 10-16mm	-	10.0 - 16.0	1
62200438	Clamp round 17-25mm	-	17.0 - 25.0	1
62200439	Clamp round 26-36mm	-	26.0 - 36.0	1

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16