

## Cable trolley system steel wire

Lapp Group offers a complete cable trolley system both for flat cables and for round cables.

### Info

For cables with lower weight (e.g. pendant station application)



### Benefits

Gentle cable clamps prevent the cables from sharp bends

### Application range

For hoisting equipment and conveyor systems  
Mechanical engineering  
Not suitable for applications in explosive environments

### Note

Round- and flat cables are not allowed to be combined side by side or below each other  
Don't assemble more than three clamps for round cables below each other  
Bending radius on the bracket corresponds to a fixed installation

### Product Make-up

The installation of a system depends on various criteria, e.g. maximum cable slack (cable weight) and working length.

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC002935 ETIM 5.0 Class-Description: Accessories for cable carrying system
General:	Max. cable load: 6 kg
Material:	Metal parts: Galvanized steel Clamps: Polyamide 6
Temperature range:	-40°C to +120°C

### Note

CIBES® is a registered trade mark of INOMEK AB  
Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (19.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**Cable trolley system steel wire**

Article number	Article designation	Max. flat cable dimensions mm	max. round cable diameter mm	Pieces / PU
Cable trolley flat cables				
62200554	Cable trolley flat steel wire	15.0 x 44.0	-	-
62200555	Mounting plate end clamp flat steel wire	15.0 x 44.0	-	-
62200556	Towing trolley flat steel wire	15.0 x 44.0	-	-
Cable trolley round cable				
62200557	Cable trolley round steel wire	-	-	-
62200559	Mounting plate end clamp round steel wire	-	-	-
62200558	Towing trolley round steel wire	-	-	-
62200437	Clamp round 10-16mm	-	10.0 - 16.0	1
62200438	Clamp round 17-25mm	-	17.0 - 25.0	1
62200439	Clamp round 26-36mm	-	26.0 - 36.0	1
Fastening components				
62200561	Tension bracket steel wire	-	-	-
62200562	Tension screw steel wire	-	-	-
62200565	Steel wire	-	-	-
62200563	Steel wire PVC covered	-	-	-

Last Update (19.12.2022)

©2022 Lapp Group - Technical changes reserved

 Product Management [www.lappkabel.de](http://www.lappkabel.de)

 You can find the current technical data in the corresponding data sheet.  
 PN 0456 / 02\_03\_16