

EASY STRIP stripping and cutting tool

Self-adjusting stripping tool with changeable cartridges/stripping knives, flexible, ergonomic design, reliable, also for Teflon/PTFE cables



Benefits

Easy to handle due to the automatic adjustment for the different crimping cross-sections

Broad application range thanks to changeable stripping cartridges

Adjusting lever for fine-adjustments ensures that the insulation (particular small dimensions) can be removed without damaging the conductors

Long durability- tested for more than 150.000 stripping operations

Ergonomic design due to the soft handle, optimised grip-width, angled-head and light construction

Application range

Stripping cassettes enable precise stripping of different insulation materials (e.g. PVC/PTFE) and diameters with a single tool

For standard cables and conductors (90 % of all applications can be stripped without setting the tool manually)

Product Make-up

Two different designs available- pistol shaped (RA) or standard version

Note

No MTW single wires 16 mm² can be machined

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000163

ETIM 5.0 Class-Description: Cable stripping tool

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000163

ETIM 6.0 Class-Description: Cable stripping tool

General:

Stripping range: 0.02 - 16.0 mm²

Weight:

136 g

Length:

Overall dimensions: L x H x W:

Standard version: 191x123x20 mm

RA version: 144x186x23 mm

Info:

Cutting capacity:

Solid cables - 1.5 mm²

Flexible conductors - up to 10 mm²

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EASY STRIP stripping and cutting tool

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EASY STRIP stripping and cutting tool

Article number	Article designation	For mm²	Colour	For insulation	Cartridge shape	Pieces / PU
Tool standard version with cartridge						
61735800	EASY STRIP incl.straight cartridge	0.02 - 10	black	PVC etc.	straight	1
61735805	EASY STRIP incl. V-cartridge	0.1 - 4	blue	PTFE etc.	V-form	1
61735807	EASY STRIP incl. O-cartridge	4 - 16	red	PVC etc.	round	1
Tool RA version with cartridge						
61735813	EASY STRIP RA incl.straight cartridge	0.02 - 10	black	PVC etc.	straight	1
61735814	EASY STRIP RA incl. V-cartridge	0.1 - 4	blue	PTFE etc.	V-form	1
61735815	EASY STRIP RA incl. O-cartridge	4 - 16	red	PVC etc.	round	1
Cartridges and replacement items						
61735801	Straight cartridge	0.02 - 10	black	PVC etc.	straight	1
61735803	V-cartridge	0.1 - 4	blue	PTFE etc.	V-form	1
61735802	O-cartridge	4 - 16	red	PVC etc.	round	1
61735806	EASY STRIP support jaws	-	-	-	-	2