

## Shrink tube PROTECT Set

Shrink tube PROTECT Set contains an assortment of common shrinking tube sizes of PROTECT in an handy box. Set is mainly used for repair and maintenance purposes.



Good chemical resistance



Assembly time

### Benefits

Convenient plastic kit with PROTECT shrink tubes including small hot air pistol

### Application range

For repair and maintenance, for small series production and in research and development

### Product features

Flame-retardant (except colour: clear)

Silicone-free

UV-resistant (only colour: black)

### Norm references / Approvals

UL 224 approval (except colour: transparent)

UL file no.: E476215 (except colour: transparent)

### Note

Not resistant against engine oils

### Included

The shrink set in a practical case

Assortment of common shrinking tube sizes of type PROTECT

Content:

50x 50 mm Shrink tube PROTECT 1,6/0,8 BK

50x 50 mm Shrink tube PROTECT 1,6/0,8 TR

Last Update (18.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## Shrink tube PROTECT Set

50 x 50 mm Shrink tube PROTECT 2,4/1,2 BK  
50 x 50 mm Shrink tube PROTECT 2,4/1,2 TR  
20 x 50 mm Shrink tube PROTECT 3,2/1,6 BK  
20 x 50 mm Shrink tube PROTECT 3,2/1,6 TR  
20 x 50 mm Shrink tube PROTECT 3,2/1,6 YE  
20 x 50 mm Shrink tube PROTECT 3,2/1,6 WH  
10 x 50 mm Shrink tube PROTECT 4,8/2,4 BK  
10 x 50 mm Shrink tube PROTECT 4,8/2,4 TR  
10 x 50 mm Shrink tube PROTECT 4,8/2,4 YE  
10 x 50 mm Shrink tube PROTECT 4,8/2,4 BU  
15 x 50 mm Shrink tube PROTECT 6,4/3,2 BK  
15 x 50 mm Shrink tube PROTECT 6,4/3,2 WH  
15 x 50 mm Shrink tube PROTECT 6,4/3,2 YE  
15 x 50 mm Shrink tube PROTECT 6,4/3,2 BU  
15 x 50 mm Shrink tube PROTECT 9,5/4,7 BK  
15 x 50 mm Shrink tube PROTECT 9,5/4,7 BU  
20 x 50 mm Shrink tube PROTECT 12,7/6,4 BK  
20 x 50 mm Shrink tube PROTECT 12,7/6,4 RD  
5 x 100 mm Shrink tube PROTECT 19,1/9,5 BK  
5 x 100 mm Shrink tube PROTECT 19,1/9,5 BU  
5 x 180 mm Shrink tube PROTECT 25,4/12,7 BK  
1 x HOT GUN

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000217 ETIM 5.0 Class-Description: Heat-shrink tubing
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000217 ETIM 6.0 Class-Description: Shrink tubing
Note:	Thin walled Dielectric strength: 20 kV/mm
Info:	Shrinking ratio: 2:1
Material:	Cross-linked polyolefin
Temperature range:	-55°C to +135°C Shrinking temperature: +90°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**Shrink tube PROTECT Set**

Article number	Article description
61742465	PROTECT Set

Last Update (18.09.2020)

©2020 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03.16