

Temflex™ 1500 insulating tape

Temflex™ 1500- is an universal electrical tape with adhesive layer made of PVC. It is waterproof and fulfils the VDE requirements.



Good chemical resistance



Waterproof

Benefits

Waterproof
 Adhesive on one side
 Resistant to most solvents
 Self-extinguishing

Application range

Multipurpose insulating tape made from PVC
 Universal electrical insulating tape for insulating, bundling, marking

Norm references / Approvals

Type acc. to VDE: type 5

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000128 ETIM 5.0 Class-Description: Adhesive tape
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000128 ETIM 6.0 Class-Description: Adhesive tape
Note:	Ultimate elongation: 170 % Tear strength: 20 N / 10 mm
Info:	Thickness: 0.15 mm
Material:	PVC
Test voltage:	Dielectric strength: 40 kV/mm

Last Update (10.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

Temflex™ 1500 insulating tape

Temperature range: 0 °C to +90 °C














Note

Temflex™ 1183 is a registered trademark of 3M

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Temflex™ 1500 insulating tape

Article number	Article designation	Colour	Length (m) x tape width (mm) x thickness (mm)	Material	Pieces / PU
61721040	Temflex  1015	white	10.0 x 15.0 x 0.15	PVC	10
61721030	Temflex  1015	black	10.0 x 15.0 x 0.15	PVC	10
61721050	Temflex  1015	green	10.0 x 15.0 x 0.15	PVC	10
61721060	Temflex  1015	blue	10.0 x 15.0 x 0.15	PVC	10
61721070	Temflex  1015	red	10.0 x 15.0 x 0.15	PVC	10
61721080	Temflex  1015	GN-YE	10.0 x 15.0 x 0.15	PVC	10
61721045	Temflex  1015	yellow	10.0 x 15.0 x 0.15	PVC	10
61721090	Temflex  2515	black	25.0 x 15.0 x 0.15	PVC	10
61721100	Temflex  2515	white	25.0 x 15.0 x 0.15	PVC	10
61721110	Temflex  2515	blue	25.0 x 15.0 x 0.15	PVC	10
61721120	Temflex  2515	red	25.0 x 15.0 x 0.15	PVC	10
61721130	Temflex  2515	green	25.0 x 15.0 x 0.15	PVC	10
61721140	Temflex  2525	black	25.0 x 25.0 x 0.15	PVC	10

Last Update (10.12.2022)

©2022 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16