

## SKINDICHT® MA-M/PG

SKINDICHT® MA-M/PG, adapter, enables the use of PG accessories in metric threads



Mechanical resistance



Robust

### Benefits

Allows the easy transition from a metric male thread to a PG female thread.

Withstands temperatures up to +200 °C.

Available for thread sizes up to PG42 or up to M63.

Mold A in easy-grip knurled design for easy screwing in of the adapter even in oily environments; mold B in smooth design.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

### Application range

For applications with different types of threads.

Withstands high chemical and mechanical stress.

Suitable for outdoor use.

### Product Make-up

Metric connection thread acc. to DIN EN 60423

Basis for technical information DIN IEC 62444

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 Class-Description: Cable screw gland

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class-Description: Cable screw gland

On request:

with O-ring fitted

Material:

Nickel-plated brass

Temperature range:

-60 °C to +200 °C

Last Update (25.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## SKINDICHT® MA-M/PG

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

# SKINDICHT® MA-M/PG

| Article number       | Thread, male M1 | Thread, female PG | Pieces / PU |
|----------------------|-----------------|-------------------|-------------|
| SKINDICHT® MA-M / PG |                 |                   |             |
| 52104200             | 16 x 1.5        | 7                 | 100         |
| 52104210             | 20 x 1.5        | 9                 | 50          |
| 52104220             | 25 x 1.5        | 11                | 50          |
| 52104230             | 25 x 1.5        | 13.5              | 50          |
| 52104240             | 25 x 1.5        | 16                | 50          |
| 52104250             | 32 x 1.5        | 16                | 25          |
| 52104260             | 32 x 1.5        | 21                | 25          |
| 52104270             | 40 x 1.5        | 21                | 25          |
| 52104280             | 50 x 1.5        | 29                | 10          |
| 52104290             | 63 x 1.5        | 36                | 10          |
| 52104300             | 63 x 1.5        | 42                | 10          |
| 52104220LF           | 25 x 1.5        | 11                | 50          |
| 52104230LF           | 25 x 1.5        | 13.5              | 50          |
| 52104240LF           | 25 x 1.5        | 16                | 50          |
| 52104250LF           | 32 x 1.5        | -                 | 25          |
| 52104260LF           | 32 x 1.5        | 21                | 25          |
| 52104270LF           | 40 x 1.5        | 21                | 25          |
| 52104280LF           | 50 x 1.5        | 29                | 10          |
| 52104290LF           | 63 x 1.5        | 36                | 10          |
| 52104300LF           | 63 x 1.5        | 42                | 10          |