

UNITRONIC® PUR CP (TP)

Screened data transmission cable with PUR outer sheath and twisted pairs for harsh conditions

UNITRONIC® PUR CP (TP): Low-frequency PUR data cable, PVC cores DIN 47100 Twisted pairs, Screened, PUR jacket, Outdoor, Flame retardant, Oil/ Abrasion resistant

Info

TP = twisted pair



Mechanical resistance



Oil-resistant



Interference signals



UV-resistant

Benefits

Data transmission cable with PUR sheath for increased mechanical stress, wear- and tear-resistant

Increased durability under harsh conditions thanks to robust PUR outer sheath

Overall braid minimises electrical interference

Decoupling of circuits by means of twisted-pair (TP) design (crosstalk effects)

Application range

For harsh environmental conditions where robust and screened cables with small dimensions are necessary

Product features

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

UNITRONIC® PUR CP (TP)

Low-adhesive surface
PUR outer sheath is resistant to most oils and hydraulic fluids
Special notch and tear-resistance
Good UV-resistance
Flame-retardant according IEC 60332-1-2

Norm references / Approvals

Based on VDE 0812

Product Make-up

Fine-wire strand made of bare copper wires
Core insulation made of PVC
TP structure
Tinned-copper braiding
Outer sheath made of PUR
Outer sheath colour: pebble grey (RAL 7032)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	DIN 47100, refer to Appendix T9
Mutual capacitance:	C/C: approx. 120 nF/km C/S: approx. 160 nF/km
Inductivity:	approx. 0.65 mH/km
Conductor stranding:	Fine copper wire strands
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 6 x outer diameter
Temperature range:	Occasional flexing: -5 °C to +70 °C Fixed installation: -40 °C to +80 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

UNITRONIC® PUR CP (TP)

Article number	Number of pairs and conductor cross section (mm ²)	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
UNITRONIC® PUR CP (TP)				
0032850	2 x 2 x 0.25	6.3	28	54
0032851	3 x 2 x 0.25	7.1	40	66
0032852	4 x 2 x 0.25	7.6	45	81
0032854	6 x 2 x 0.25	8.5	70	115
0032860	2 x 2 x 0.5	7.9	48	93
0032861	3 x 2 x 0.5	8.7	74	129
0032862	4 x 2 x 0.5	9.4	82	146
0032864	6 x 2 x 0.5	11.1	110	198

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16