

## EPIC® SENSOR Flush-type M8

sensor/actuator flush-type connectors with TPE single strands for front-mounting (A-coded)



Supplementary automation components from Lapp



Mechanical and plant engineering



Space requirement



Waterproof

### Benefits

Flexible connection solutions for individual device concepts  
Simple installation in devices (e.g. cabinet)

### Application range

Connection of enclosures and cabinets

### Product features

M8 fastening thread  
Designs for front mounting  
PWIS-free

### Product Make-up

TPE single strands, l = 0.5 m  
Core cross section: 0.25 mm<sup>2</sup>

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002061

ETIM 5.0 Class-Description: Sensor-actuator connector chassis

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002061

ETIM 6.0 Class-Description: Sensor-actuator connector chassis

Material:

Contact: CuSn

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® SENSOR Flush-type M8

Protection rating:	Contact surface: Ag IP 67
Ambient temperature (operation):	Plug/socket -25°C to +85°C
Coding:	A-standard
Rated current (A):	4 A

### Note

Copper price basis: inclusive of copper. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

## EPIC® SENSOR Flush-type M8

Article number	Article designation	Number of pins	Rated voltage (V)	PU
Panel-mount connector male				
22260100	AB-C3-M8MS-0,5	3	60	1
22260101	AB-C4-M8MS-0,5	4	30	1
Panel-mount connector female				
22260102	AB-C3-M8FS-0,5	3	60	1
22260103	AB-C4-M8FS-0,5	4	30	1