


## EPIC® H-B 32 AG

Housing design H-B for 2 inserts.

The connector housing consists of built-in housing, 2 double levers and a seal. It is suitable for use in control systems application.



### Benefits

Two inserts in one housing. With two levers for high safety

### Application range

Plant engineering  
Control engineering  
Plastics industry

### Product features

H-A case: Wall base  
Dual levers  
Included: flat gasket

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 Class-Description: Housing for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

Material:

Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel

Sealing: NBR

Protection rating:

IP 65 (latched)

Temperature range:

-40 °C to +100 °C, short-term up to +125 °C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (05.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

**EPIC® H-B 32 AG**

Article number	Article description	M	Pieces / PU
H-B housing: panel-mount base (double lever)			
10132000	H-B 32 AG	AG	5