

EPIC® H-B 6 TGH

Housing design H-B. The industry standard.

The robust metal housing is ideal for use in investment construction and the plastics industry and has a direct cable entry.

Info

Non-slip ridges for comfortable disconnecting

More interior space for wiring

Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

The smallest housing out of the H-B series. For inserts with high electrical properties

Application range

Plant engineering

Control engineering

Plastics industry

Product features

Hood, high version

Last Update (23.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 6 TGH

Bolts for single lever
Straight cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000437 ETIM 5.0 Class-Description: Housing for industrial connectors
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000437 ETIM 6.0 Class-Description: Housing for industrial connectors
Material:	Housing: powder-coated aluminium alloy, grey Bolts: steel, coated
Protection rating:	IP 65 (latched) NEMA 250, UL50E: 12, 4 (latched)
VDE-tested:	Certified production control: VDE-REG. no.: B437 UL-tested: UL File Number: E75770
Temperature range:	-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 6 TGH

Article number	Article description	M	PG	Neck	Pieces / PU
H-B housing: hood (straight cable entry, bolts for single lever, high version)					
70020200	EPIC® H-B 6 TGH 21	-	21	yes	10
70020400	EPIC® H-B 6 TGH 29	-	29	yes	10
79020000	EPIC® H-B 6 TGH M16	16	-	-	10
79020100	EPIC® H-B 6 TGH M20	20	-	-	10
79020200	EPIC® H-B 6 TGH M25	25	-	-	10
79020400	EPIC® H-B 6 TGH M32	32	-	-	10

EPIC® H-B 6 TGH

