

EPIC® MH 10.0mm Contacts

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

-

Info

Crimping contacts for maximum cross sections and currents

Modular connector system, mateable with the market standard



Supplementary automation components from Lapp



Mechanical and plant engineering



Rail



Wind Energy



Suitable for outdoor use



Robust



Voltage

Benefits

Male and female contacts with silver plating

Crimping with Klauke D 22 and HD 13 series

Cross section: 25, 35, 50, 70 and 95 mm²

Application range

Mechanical engineering

Renewable energy

Test equipment building

Last Update (06.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® MH 10.0mm Contacts

Plant engineering
Railway applications / vehicle construction

Technical Data

Termination methods:	Crimp termination: 25mm ² ... 95mm ²
Stripping length (mm):	23
Material:	brass silver plated CuZn / Ag
Cycle of mechanical operation:	500

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MH 10.0mm Contacts

Article number	Article description	Contact type	Connection cross section (mm ²)	Pieces / PU
EPIC® MH 10.0mm operating contacts				
44423330	EPIC® MH SCEM AG 25sqmm D=10.0	male	25	10
44423331	EPIC® MH BCEM AG 25sqmm D=10.0	female	25	10
44423332	EPIC® MH SCEM AG 35sqmm D=10.0	male	35	10
44423333	EPIC® MH BCEM AG 35sqmm D=10.0	female	35	10
44423334	EPIC® MH SCEM AG 50sqmm D=10.0	male	50	10
44423335	EPIC® MH BCEM AG 50sqmm D=10.0	female	50	10
44423336	EPIC® MH SCEM AG 70sqmm D=10.0	male	70	10
44423337	EPIC® MH BCEM AG 70sqmm D=10.0	female	70	10
44423338	EPIC® MH SCEM AG 95sqmm D=10.0	male	95	10
44423339	EPIC® MH BCEM AG 95sqmm D=10.0	female	95	10