

EPIC® MH 1.0mm contacts machined

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

-

Info

Machined gold plated contacts with 1mm diameter for EPIC® MH Gigabit module
Gold-plated contacts for low transfer resistance



Benefits

Machined gold plated contacts with 1mm diameter for EPIC® MH Gigabit module
Gold-plated contacts for low transfer resistance

Application range

Mechanical and plant engineering
Robotics industry
Renewable energy
Railway applications / vehicle construction

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000796 ETIM 5.0 Class-Description: Contact for industrial connectors
Stripping length (mm):	4.2 ± 0.5mm
Material:	brass gold plated CuZn / Au
Cycle of mechanical operation:	500

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MH 1.0mm contacts machined

Article number	Article description	Contact type	Conductor cross-section AWG	Pieces / PU
44423285	EPIC® MH SCEM AU 0.09 - 0.25sqmm D=1.0	male	28.0 - 24.0	100
44423286	EPIC® MH BCEM AU 0.09 - 0.25sqmm D=1.0	female	28.0 - 24.0	100
44423287	EPIC® MH SCEM AU 0.13 - 0.33sqmm D=1.0	male	26.0 - 22.0	100
44423288	EPIC® MH BCEM AU 0.13 - 0.33sqmm D=1.0	female	26.0 - 22.0	100
44423289	EPIC® MH SCEM AU 0.25 - 0.52sqmm D=1.0	male	24.0 - 20.0	100
44423290	EPIC® MH BCEM AU 0.25 - 0.52sqmm D=1.0	female	24.0 - 20.0	100