


EPIC® MH PE 10.0mm Contacts

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

-

Info

Protection earth (PE) crimping contacts for maximum cross sections
Modular connector system, mateable with the market standard



Benefits

Male and female contacts with silver plating and approx. 14cm stranded wire to connect the PE Pin of the EPIC® MH Multiframe
Crimping with Klauke D 22 and HD 13 series
Cross section: 25, 35, 50, 70 and 95 mm²

Application range

Mechanical engineering
Renewable energy
Test equipment building
Plant engineering
Railway applications / vehicle construction

Technical Data

Termination methods:	Crimp termination: 25mm ² ... 95mm ² Stranded wire for PE connection to the module frame
Stripping length (mm):	20
Material:	brass silver plated CuZn / Ag
Cycle of mechanical operation:	500

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MH PE 10.0mm Contacts

Article number	Article description	Contact type	Connection cross section (mm ²)	PL_VERPACKUNGSEINHEIT1
EPIC® MH 10.0mm protection earth contacts				
44423344	EPIC® MH PE SCEM AG 25sqmm D=10.0	male	25	1
44423345	EPIC® MH PE BCEM AG 25sqmm D=10.0	female	25	1
44423346	EPIC® MH PE SCEM AG 35sqmm D=10.0	male	35	1
44423347	EPIC® MH PE BCEM AG 35sqmm D=10.0	female	35	1
44423348	EPIC® MH PE SCEM AG 50sqmm D=10.0	male	50	1
44423349	EPIC® MH PE BCEM AG 50sqmm D=10.0	female	50	1
44423350	EPIC® MH PE SCEM AG 70sqmm D=10.0	male	70	1
44423351	EPIC® MH PE BCEM AG 70sqmm D=10.0	female	70	1
44423352	EPIC® MH PE SCEM AG 95sqmm D=10.0	male	95	1
44423353	EPIC® MH PE BCEM AG 95sqmm D=10.0	female	95	1