

EPIC® MC Module: Koax 3pole

The mixed assembly guarantees high flexibility. For applications in machine and plant engineering, for robotics and slide-in technology.

The three-pole coaxial module is suitable for transmission of RGB video signal in a single module. It combines more functions in single connector, which therefore makes it more flexible.

Info

RGB video signal transmission in one module



Supplementary automation components from Lapp



Mechanical and plant engineering



Wind Energy

Benefits

The mix of different functions in one plug guarantees high flexibility
Assembly of individual connectors, suitable for different applications

Application range

Plant engineering
Light & sound technology
Control engineering

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC002641

ETIM 5.0 Class-Description: Modular connector (industrial connector)

Classification ETIM 6:

ETIM 6.0 Class-ID: EC002641

ETIM 6.0 Class-Description: Modular connector (industrial connector)

Rated voltage (V):

250 V

Pollution degree:

3

Last Update (24.04.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® MC Module: Koax 3pole

Contact resistance:	< 2,7 mOhm
Contacts:	Copper alloy, gold-plated
Number of contacts:	3
Termination methods:	Solder termination: var. coax cables
Cycle of mechanical operation:	100
Temperature range:	-40 °C to +100 °C, short-term up to +125 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® MC Module: Koax 3pole

Article number	Article description	Contact type	Number of operating contacts	Slots	Pieces / PU
Module: 3-pin coax					
10399200	MCS 3 coax	male	3	1	10
10399300	MCB 3 coax	female	3	1	10