

ÖLFLEX® HEAT 350 MC

Suitable for use in ambient temperature from -50 °C to +350 °C

ÖLFLEX® HEAT 650 SC - Glass fibre insulated power cable for use in blast furnaces, glassworks, motor construction etc. at ambient temperatures up to +350 °C

Info

Voltage rating: 230/400 V

For use in dry conditions



Halogen-free



Heat-resistant



Cold-resistant



Temperature-resistant

Benefits

Low conductor-resistance due to the nickel-plated copper conductors

Wide operating temperature range allows the product to be used in applications under Thermal Class C (>180 °C).

Application range

Blast furnaces and glassworks
Chemical and power station construction
Motor and furnace construction
Extrusion and drying systems
Lighting, apparatus and instrument industry

ÖLFLEX® HEAT 350 MC

Product features

Flame-retardant

Halogen-free

Only suitable for use in dry conditions

ÖLFLEX® HEAT 1565 MC is recommended if the peak temperature of the application may briefly go beyond 350°C

Product Make-up

Fine-wire strand made of nickel-plated copper

Core insulation: glass fibre covering and impregnated glass fibre braids

Cores twisted together

Outer sheath: impregnated glass fibre braiding, white (natural)

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001578

ETIM 5.0 Class-Description: Flexible cable

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001578

ETIM 6.0 Class-Description: Flexible cable

Core identification code:

Colours according to VDE 0293-308, refer to Appendix T9

Conductor stranding:

Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5

Minimum bending radius:

Fixed installation: 6 x outer diameter

Nominal voltage:

U0/U 230/400 V

Test voltage:

1500 V

Temperature range:

Fixed installation: -50°C to +350°C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: Coil ≤ 30 kg, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® HEAT 350 MC

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® HEAT 350 MC				
0091375	2 X 1.0	6.8	19.2	56
0091376	3 G 1.0	7.4	28.8	70
0091377	4 G 1.0	8.2	38.4	88
0091380	2 X 1.5	7.8	28.8	77
0091381	3 G 1.5	8.4	43.2	93
0091382	4 G 1.5	9.4	57.6	118
0091383	5 G 1.5	10.3	72	140
0091390	3 G 2.5	8.9	72	124
0091391	4 G 2.5	9.8	96	160
0091392	5 G 2.5	10.1	120	194