

SILVYN® SNAP PET

SILVYN® SNAP PET - self-wrapping braided sleeving

Info

Simple, fast cable bundling



Assembly time



Low weight



Reliability



Temperature-resistant

Benefits

Cables can be guided in or out of the SILVYN® SNAP at any point.

Self-wrapping

Simple, fast cable bundling

Tidies away cables

Protection against dust

Application range

Easy cable protection

Bundling and guiding of cables and wires

Cable harness

Product features

Abrasion-resistant

Flexible

Self-wrapping

Cut longitudinally

Product Make-up

Polyester - PET braid sidewise rolled up

Last Update (02.05.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SILVYN® SNAP PET

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001182 ETIM 5.0 Class-Description: Braided hose
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001182 ETIM 6.0 Class-Description: Braided hose
On request:	Bulk containers on rolls More sizes available
Note:	Halogen and cadmium-free Fire behaviour according to UL94 V-2
Colour delivered:	Black, grey, orange, yellow, white
Material:	Polyester - PET braid sidewise rolled up
Temperature range:	-55°C to +150°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

SILVYN® SNAP PET

Article number	Nominal size	Clamping range in mm	Colour	PU (m)
SILVYN® SNAP PET				
61721280	19	19.0 - 25.0	grey	2.5
61721281	19	19.0 - 25.0	orange	2.5
61721282	19	19.0 - 25.0	black	2.5
61721283	19	19.0 - 25.0	white	2.5
61721284	19	19.0 - 25.0	yellow	2.5