

## **KNIPEX Diagonal cutter**

KNIPEX X-Cut® Diagonal cutter with insulated handle for precise cutting

### **Info**

Narrow head style for use in confined areas



### **Benefits**

High ergonomics thanks to multi-component handles  
Insulated handles allow working under voltage up to 1000V

### **Application range**

For soft and hard wire

### **Product features**

Precision ground, hardened blades

### **Technical Data**

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000142

ETIM 5.0 Class-Description: Cable shears

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000142

ETIM 6.0 Class-Description: Cable shears

Certifications:

Insulated according to IEC 60900, applicable up to 1000V AC / 1500V DC

VDE-tested

Material:

Vanadium steel, forged, multi stage oil-hardened

### **Note**

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.

**KNIPEX Diagonal cutter**

Article number	Article designation	Soft wire mm	Medium hard wire mm	Hard wire mm	Weight (kg)	Length (mm)
KNIPEX Diagonal cutter						
62120520	Diagonal cutter SESI 16	4	3	2	0.216	160