

## EPIC® SOLAR 4 M

The make-up solar connector in 4 mm variant has double safety system and it is suitable for crystalline and thin-layered cables.

### Info

4 mm connector system with double hook  
Field-mountable solar connector



Solar Energy



Suitable for outdoor use



Voltage



Temperature-resistant



UV-resistant



Waterproof

### Benefits

Low contact-resistance for efficient power transmission  
Crimp connection for reliable field mounting  
Suitable for various ÖLFLEX® SOLAR cables

### Application range

Photovoltaic plants  
Crystalline and thin-film constructions  
Solartracker

Last Update (03.03.2026)

©2026 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## EPIC® SOLAR 4 M

### Product features

4 mm connector system with double hook  
inclusive contacts

### Technical Data

|                        |  |
|------------------------|--|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC002635<br>ETIM 5.0 Class-Description: Circular connector (industrial connector) |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC002635<br>ETIM 6.0 Class-Description: Circular connector (industrial connector) |
| Rated voltage (V):     | 1000 V AC/DC   |
| Rated impulse voltage: | 8 kV   |
| Pollution degree:      | 3  |
| Contact resistance:    | < 0.5 mOhm   |
| Protection rating:     | IP 67  |
| Protection class:      | II   |
| Temperature range:     | -40°C to +105°C  |

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.



## EPIC® SOLAR 4 M

| Article number | Article designation                                      | Cross-section (mm <sup>2</sup> ) | Clamping range in mm | Rated current (A) | PU  |
|----------------|--|----------------------------------|----------------------|-------------------|-----|
| 44428260       | EPIC® SOLAR 4 M 2.5 mm <sup>2</sup>                      | 2.5                              | 4.8 - 6.0            | 22                | 100 |
| 44428262       | EPIC® SOLAR 4 M 4mm <sup>2</sup> ...<br>6mm <sup>2</sup> | 4.0 - 6.0                        | 5.2 - 7.1            | 30                | 100 |

Last Update (03.03.2026)

©2026 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16

**EPIC® SOLAR 4 M**

