

ÖLFLEX® CLASSIC 100 YELLOW

Yellow outer sheath for special warning purposes

ÖLFLEX® CLASSIC 100 YELLOW - flexible PVC cable, colour coded. Power and control cable with yellow outer sheath for warning purposes, 450/750V, also for YSLY or YY

Info

CPR: Article number choice under www.lappkabel.com/cpr
For warning purposes



Good chemical resistance



Torsion-resistant

Benefits

High electrical performance due to 4 kV test voltage

Application range

For electrical circuits that remain 'live' after the main switch has been disconnected

Service sockets and illumination circuits

in electrical switchboards and cabinets

Suitable for torsional applications which are typical for the loop in wind turbine generators (WTG)

Product features

Flame-retardant according IEC 60332-1-2

Good chemical resistance, see catalogue appendix T1

Norm references / Approvals

Based on IEC 60227-5 and EN 50525-2-51

Last Update (17.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® CLASSIC 100 YELLOW

Product Make-up

Fine-wire strand made of bare copper wires
PVC insulation LAPP P8/1
Outer sheath: PVC, yellow (similar to RAL 1016)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001578 ETIM 5.0 Class-Description: Flexible cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001578 ETIM 6.0 Class-Description: Flexible cable
Core identification code:	VDE 0293-308, refer to Appendix T9
Conductor stranding:	Fine wire according to VDE 0295, class 5/IEC 60228 class 5
Torsion movement in WTG:	TW-0 & TW-1, refer to Appendix T0
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 4 x outer diameter
Nominal voltage:	U0/U: 450/750 VAC In protected and fixed installations: U0/U: 600/1000 V
Test voltage:	4000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Occasional flexing: -5°C to +70°C Fixed installation: -40°C to +80°C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.



ÖLFLEX® CLASSIC 100 YELLOW

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® CLASSIC 100 YELLOW; U0/U: 450/750 V				
0010400	3 G 1.5	8.1	43	95
00104023	4 G 1.5	8.9	58	117
00104033	5 G 1.5	10	72	144
0010401	3 G 2.5	9.6	72	152
00104043	4 G 2.5	10.7	96	205
00104053	5 G 2.5	11.8	120	225

Last Update (17.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16