

ÖLFLEX® HEAT 180 GLS

Steel-armoured silicone cables for increased mechanical stress

ÖLFLEX® HEAT 180 GLS - steel-armoured silicone power and control cable for use in machines, plant construction and toolbuilding for temperatures up to +180°C

Info

Protected against thermal and mechanical loads



Halogen-free



Cold-resistant



Mechanical resistance



Temperature-resistant

Benefits

Close-meshed braid made of galvanised steel wires protects against mechanical damage

Longer durability in harsh applications than conventional silicone cables

Possesses insulating properties after combustion due to remaining SiO₂ ash on the conductor

Application range

Areas with high ambient temperatures and occasionally mechanical stress

Typical fields of application

- Steel and glass works
- Cement and ceramic works
- Foundries
- Shipbuilding industry
- Furnace construction

Last Update (20.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® HEAT 180 GLS

Product features

Halogen-free (IEC 60754-1), no corrosive gases (IEC 60754-2), flame-retardant (IEC 60332-1-2)

Only suitable for use in dry conditions

Adequate ventilation must be ensured, since the mechanical properties of silicone cables decrease from +100 °C in the absence of air

Product Make-up

Fine-wire, tinned-copper conductor

Silicone-based core insulation

Cores twisted together

Silicone-based outer sheath,

colour red-brown

Glass fibre wrapping

Galvanised steel wire braiding

Technical Data

| | |
|---------------------------|---|
| Classification ETIM 5: | ETIM 5.0 Class-ID: EC001578 ETIM 5.0 Class-Description: Flexible cable |
| Classification ETIM 6: | ETIM 6.0 Class-ID: EC001578 ETIM 6.0 Class-Description: Flexible cable |
| Core identification code: | Colours according to VDE 0293-308, refer to Appendix T9 From 6 cores: black with white numbers |
| Conductor stranding: | Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5 |
| Minimum bending radius: | Occasional flexing: 20 x outer diameter Fixed installation: 4 x outer diameter |
| Nominal voltage: | U ₀ /U: 300/500 V |
| Test voltage: | 2000 V |
| Protective conductor: | G = with GN-YE protective conductor X = without protective conductor |
| Temperature range: | -50 °C to +180 °C (adequate ventilation required) |

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.



ÖLFLEX® HEAT 180 GLS

| Article number | Number of cores and mm ² per conductor | Outer diameter [mm] | Copper index (kg/km) | Weight (kg/km) |
|----------------------|---|---------------------|----------------------|----------------|
| ÖLFLEX® HEAT 180 GLS | | | | |
| 0046201 | 2 X 0.75 | 7.6 | 14.4 | 84 |
| 0046202 | 3 G 0.75 | 8 | 21.6 | 96 |
| 00462033 | 4 G 0.75 | 8.8 | 28.8 | 118 |
| 00462043 | 5 G 0.75 | 9.7 | 36 | 145 |
| 0046205 | 6 G 0.75 | 10.4 | 43.2 | 167 |
| 0046206 | 7 G 0.75 | 10.4 | 50.4 | 171 |
| 0046207 | 2 X 1.0 | 7.8 | 19.2 | 92 |
| 0046208 | 3 G 1.0 | 8.2 | 28.8 | 106 |
| 00462093 | 4 G 1.0 | 9.1 | 38.4 | 132 |
| 00462103 | 5 G 1.0 | 10 | 48 | 161 |
| 0046212 | 7 G 1.0 | 10.7 | 67 | 205 |
| 0046213 | 2 X 1.5 | 8.8 | 29 | 119 |
| 0046214 | 3 G 1.5 | 9.2 | 43 | 140 |
| 00462153 | 4 G 1.5 | 10 | 57.6 | 168 |
| 00462163 | 5 G 1.5 | 10.8 | 72 | 212 |
| 0046218 | 7 G 1.5 | 11.8 | 101 | 255 |
| 0046237 | 12 G 1.5 | 15.4 | 173 | 433 |
| 0046219 | 2 X 2.5 | 10 | 48 | 162 |
| 0046220 | 3 G 2.5 | 10.9 | 72 | 217 |
| 00462213 | 4 G 2.5 | 12 | 96 | 260 |
| 00462223 | 5 G 2.5 | 13 | 120 | 310 |
| 0046224 | 7 G 2.5 | 14 | 168 | 362 |
| 0046226 | 3 G 4.0 | 12.9 | 115 | 300 |
| 00462273 | 4 G 4.0 | 14 | 154 | 365 |
| 00462283 | 5 G 4.0 | 15.4 | 192 | 446 |
| 00462313 | 4 G 6.0 | 16.1 | 230 | 500 |
| 00462343 | 4 G 10.0 | 20.8 | 384 | 807 |
| 00462353 | 4 G 16.0 | 22.8 | 614 | 1117 |

Last Update (20.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16