

ÖLFLEX® HEAT 260 MC

Polytetrafluoroethylene cables for most extreme loads

ÖLFLEX® HEAT 260 MC - PTFE power cable, robust, chemical resistant and space-saving, for use in machine and plant construction at temperatures: -190°C to +260°C

Info

Excellent chemical, thermal and electrical performance

Thin, light and robust



Suitable for outdoor use



Good chemical resistance



Flame-retardant



Cold-resistant



Low weight



Oil-resistant



Acid-resistant



Temperature-resistant

Last Update (23.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® HEAT 260 MC



UV-resistant

Benefits

Space-saving installation due to small cable diameters
Stress crack resistant to frequent ambient temperature fluctuations
Due to good electrical and mechanical properties suitable for sensor technology
Low outgassing behaviour

Application range

For use in environments with very high operating temperatures, heavy usage of chemical agents or confined spaces
ÖLFLEX® HEAT 260 has proven to be an effective solution in harsh environments such as paint shop lines

Typical fields of application

- Industrial furnace construction
 - Foundries
 - Chemical industry
 - Power plant engineering
 - Paint shop line technology
 - Heating elements
 - Polymer processing
 - Wind turbine engineering
- Sensor systems, e.g. level sensors

Product features

ÖLFLEX® HEAT 260 made of PTFE

- Outstanding resistance against acids, alkalis, solvents, lacquers, petrol, oils and many other chemical media
 - Difficult to inflame
 - High dielectric strength and high abrasion resistance
 - Low water absorption
 - Resistant to microbes
 - Adhesion-free insulation materials
 - Weather and ozone resistant
 - Hydrophobic and dirt-repellent
 - High elongation and tear resistance
 - Resists contact with liquid nitrogen
 - Resistant against hydraulic fluids
- Flame-retardant

Product Make-up

Fine-wire strand made of nickel-plated copper
PTFE-based core insulation
Cores twisted together
PTFE-based outer sheath, black

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC001578
ETIM 5.0 Class-Description: Flexible cable

Classification ETIM 6:

ETIM 6.0 Class-ID: EC001578
ETIM 6.0 Class-Description: Flexible cable

Last Update (23.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

ÖLFLEX® HEAT 260 MC

Core identification code:	Colours according to VDE 0293-308, refer to Appendix T9
Conductor stranding:	Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 4 x outer diameter
Nominal voltage:	U0/U: 300/500 V
Test voltage:	2500 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Fixed installation: -190 °C bis +260 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**ÖLFLEX® HEAT 260 MC**

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® HEAT 260 MC				
0091300	2 X 0.5	3.9	9.6	22
0091301	3 G 0.5	4.1	14.4	33
0091302	4 G 0.5	4.5	19.2	45
0091305	2 X 0.75	4.2	14.4	32
0091306	3 G 0.75	4.4	21.6	47
0091307	4 G 0.75	5.1	28.8	58
0091310	2 X 1.0	4.8	19.2	42
0091311	3 G 1.0	5.1	28.8	56
0091312	4 G 1.0	5.8	38.4	71
0091315	3 G 1.5	5.6	43.2	72
0091316	4 G 1.5	6.1	57.6	98
0091317	5 G 1.5	7	72	118
0091320	3 G 2.5	7.1	72	87
0091321	4 G 2.5	7.7	96	116
0091322	5 G 2.5	8.5	120	145

Last Update (23.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03_16