

Polytetrafluoroethylene cables for most extreme loads

ÖLFLEX® HEAT 260 MC - PTFE power cable, robust, chemical resistant and space-saving, for use in machine and plant construction at temperatures: -190°C to +260°C

### Info

Excellent chemical, thermal and electrical performance
Thin, light and robust





Suitable for outdoor use



Good chemical resistance



Flame-retardant



Cold-resistant



Low weight



Oil-resistant



Acid-resistant



Temperature-resistant

Last Update (27.07.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02\_03.16





### **Benefits**

Space-saving installation due to small cable diameters
Stress crack resistant to frequent ambient temperature fluctuations
Due to good electrical and mechanical properties suitable for sensor technology
Low outgassing behaviour

### **Application range**

For use in environments with very high operating temperatures, heavy usage of chemical agents or confined spaces ÖLFLEX® HEAT 260 has proven to be an effective solution in harsh environments such as paint shop lines Typical fields of application

- Industrial furnace construction
- Foundries
- Chemical industry
- Power plant engineering
- Paint shop line technology
- Heating elements
- Polymer processing
- Wind turbine engineering

Sensor systems, e.g. level sensors

### **Product features**

ÖLFLEX® HEAT 260 made of PTFE

- Outstanding resistance against acids, alkalis, solvents, lacquers, petrol, oils and many other chemical media
- Difficult to inflame
- High dielectric strength and high abrasion resistance
- Low water absorption
- Resistant to microbes
- Adhesion-free insulation materials
- Weather and ozone resistant
- Hydrophobic and dirt-repellent
- High elongation and tear resistance
- Resists contact with liquid nitrogen
- Resistant against hydraulic fluids

Flame-retardant

### **Product Make-up**

Fine-wire strand made of nickel-plated copper PTFE-based core insulation Cores twisted together PTFE-based outer sheath, black

## **Technical Data**

Classification ETIM 5: ETIM 5.0 Class-ID: EC001578

ETIM 5.0 Class-Description: Flexible cable

Classification ETIM 6: ETIM 6.0 Class-ID: EC001578

ETIM 6.0 Class-Description: Flexible cable

Last Update (27.07.2025)

©2025 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16





Core identification code: Colours according to VDE 0293-308, refer to Appendix T9

Conductor stranding: Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5

Minimum bending radius:

Occasional flexing: 15 x outer diameter
Fixed installation: 4 x outer diameter

Nominal voltage: U0/U: 300/500 V

Test voltage: 2500 V

Protective conductor: G = with GN-YE protective conductor

X = without protective conductor

Temperature range: Fixed installation:-190 °C bis +260 °C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® HEAT 260 MC	;	•		
0091300	2 X 0.5	3.9	9.6	22
0091301	3 G 0.5	4.1	14.4	33
0091302	4 G 0.5	4.5	19.2	45
0091305	2 X 0.75	4.2	14.4	32
0091306	3 G 0.75	4.4	21.6	47
0091307	4 G 0.75	5.1	28.8	58
0091310	2 X 1.0	4.8	19.2	42
0091311	3 G 1.0	5.1	28.8	56
0091312	4 G 1.0	5.8	38.4	71
0091315	3 G 1.5	5.6	43.2	72
0091316	4 G 1.5	6.1	57.6	98
0091317	5 G 1.5	7	72	118
0091320	3 G 2.5	7.1	72	87
0091321	4 G 2.5	7.7	96	116
0091322	5 G 2.5	8.5	120	145