ÖLFLEX® CLASSIC 110 BLACK 0,6/1 kV

ÖLFLEX® CLASSIC 110 BLACK 0,6/1kV: power and control cable for various applications, PVC, conductor class 5, black cores, number coded, outdoors

Info

Good outdoor performance
CPR: Article number choice under www.lappkabel.com/cpr

Suitable for outdoor use

Torsion-resistant

UV-resistant

Application range

Plant engineering, industrial machinery, heating and air-conditioning systems, power stations, stage applications
For fixed installation as well as occasional flexing at free, non-continuously recurring movement without tensile load
Each dimension with nominal/ minimum average wall thickness of the outer sheath of at least 1.8 mm: For applications where a strengthened outer sheath may turn out to be advantageous
Suitable for torsional applications which are typical for the loop in wind turbine generators (WTG)

Product features

Flame-retardant according IEC 60332-1-2
UV and weather-resistant according to ISO 4892-2
Ozone-resistant according to EN 50396

Norm references / Approvals

Based on VDE 0250-1 and HD 627-1 S1

Product Make-up

Last Update (25.01.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

ÖLFLEX® CLASSIC 110 BLACK 0,6/1 kV

Fine-wire strand made of bare copper wires
PVC insulation LAPP P8/1
PVC outer sheath, black (RAL 9005)

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	Black with white numbers acc. to VDE 0293-334
Conductor stranding:	Fine wire according to VDE 0295, class 5/IEC 60228 class 5
Torsion movement in WTG:	TW-0 & TW-1, refer to Appendix T0
Minimum bending radius:	Static/Occ. moved: 4/15xOD*
Nominal voltage:	U0/U: 600/1000 V
Test voltage:	4000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Occasional flexing: -5 °C to +70 °C Fixed installation: -40 °C to +80 °C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.
Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.
Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths
Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum
Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

©2026 Lapp Group - Technical changes reserved

LAPP

PRODUCT INFORMATION

ÖLFLEX® CLASSIC 110 BLACK 0,6/1 kV

Article number	Number of cores and mm² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® CLASSIC 110 BLACK				
1120232	2 X 0.75	8.3	14.4	81
1120233	3 G 0.75	8.7	21.6	93
1120234	3 X 0.75	8.7	21.6	93
1120235	4 G 0.75	9.2	29	108
1120237	5 G 0.75	9.9	36	126
1120241	7 G 0.75	10.7	51	162
1120248	12 G 0.75	13.4	86	236
1120251	18 G 0.75	15.4	130	334
1120259	41 G 0.75	21.6	296	713
1120266	2 X 1.0	8.6	19.2	98
1120267	3 G 1.0	9	29	112
1120268	3 X 1.0	9	29	112
1120269	4 G 1.0	9.6	38.4	131
1120270	4 X 1.0	9.6	38.4	131
1120271	5 G 1.0	10.4	48	152
1120274	7 G 1.0	11.1	67	196
1120280	12 G 1.0	14	116	286
1120284	18 G 1.0	16.1	173	419
1120290	25 G 1.0	18.6	240	572
1120294	34 G 1.0	21.3	326	764
1120298	41 G 1.0	23.2	394	891
1120306	2 X 1.5	9.6	29	123
1120307	3 G 1.5	10.1	43	165
1120308	3 X 1.5	10.1	43	144
1120309	4 G 1.5	10.8	58	170
1120311	5 G 1.5	11.7	72	199
1120314	7 G 1.5	12.6	101	261
1120320	12 G 1.5	16.1	173	399
1120322	14 G 1.5	17	202	448
1120324	18 G 1.5	18.8	259	547
1120328	25 G 1.5	21.7	360	770
1120330	34 G 1.5	24.9	490	996
1120333	50 G 1.5	29.8	720	1427

Last Update (25.01.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

ÖLFLEX® CLASSIC 110 BLACK 0,6/1 kV

Article number	Number of cores and mm² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1120339	2 X 2.5	10.8	48	147
1120340	3 G 2.5	11.3	72	182
1120342	4 G 2.5	12.2	96	225
1120343	4 X 2.5	12.2	96	225
1120344	5 G 2.5	13.3	120	266
1120346	7 G 2.5	14.4	168	354
1120349	12 G 2.5	18.7	288	540
1120350	14 G 2.5	19.8	336	613
1120351	18 G 2.5	22	432	788
1120353	25 G 2.5	25.8	600	1094
1120360	4 G 4.0	13.8	154	324
1120361	5 G 4.0	15.1	192	385
1120362	7 G 4.0	16.4	269	513
1120366	4 G 6.0	15.1	230	442
1120367	5 G 6.0	16.8	288	526
1120368	7 G 6.0	18.2	403	705
1120370	4 G 10.0	18.7	384	707
1120371	5 G 10.0	20.7	480	881
1120374	4 G 16.0	21.3	614	1100
1120375	5 G 16.0	23.6	768	1350
1120376	7 G 16.0	26.2	1075	1800
1120378	4 G 25.0	26.2	960	1600
1120379	5 G 25.0	29	1200	2050
1120382	4 G 35.0	29.1	1344	2400
1120383	5 G 35.0	32.5	1680	2900
1120385	4 G 50.0	35.6	1920	3400
1120387	4 G 70.0	40.7	2688	5050
1120389	4 G 95.0	46.8	3648	6010
1120390	4 G 120.0	53.5	4608	7500

Last Update (25.01.2026)
©2026 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16