

## ÖLFLEX® CLASSIC 110 CY BLACK 0,6/1 kV


ÖLFLEX® CLASSIC 110 CY BLACK 0,6/1 kV power and control cable, various applications, PVC, conductor class 5, number coded black cores, screened, outdoor

### Info

Good outdoor performance

EMC/Screened

CPR: Article number choice under [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)



Suitable for outdoor use



Interference signals



UV-resistant

### Application range

Plant engineering

Industrial machinery

Heating and air-conditioning systems

Power stations

For frequency converter-powered 3-phase AC motors

In EMC-sensitive environments

(electromagnetic compatibility)

Servo Drive Connection Cable

For fixed installation as well as occasional flexing at free, non-continuously recurring movement without tensile load

Each dimension with nominal/ minimum average wall thickness of the outer sheath of at least 1.8 mm: For applications where a strengthened outer sheath may turn out to be advantageous

### Product features

Flame-retardant according IEC 60332-1-2

UV and weather-resistant according to ISO 4892-2

Last Update (11.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## ÖLFLEX® CLASSIC 110 CY BLACK 0,6/1 kV

Ozone-resistant according to EN 50396  
High degree of screening  
low transfer impedance  
(max. 250 Ω/km at 30 MHz)

### Norm references / Approvals

Based on VDE 0250-1 and HD 627-1 S1

### Product Make-up

Fine-wire strand made of bare copper wires  
PVC insulation LAPP P8/1  
PVC inner sheath, black  
Tinned-copper braiding  
PVC outer sheath, black (RAL 9005)

### Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class-Description: Control cable
Core identification code:	Black with white numbers acc. to VDE 0293-334
Conductor stranding:	Fine wire according to VDE 0295, class 5/IEC 60228 class 5
Minimum bending radius:	Static/Occ. moved: 6/20xOD*
Nominal voltage:	U0/U: 600/1000 V
Test voltage:	4000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Occasional flexing: -5°C to +70°C Fixed installation: -40°C to +80°C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: [www.lappkabel.de/en/cable-standardlengths](http://www.lappkabel.de/en/cable-standardlengths)

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**ÖLFLEX® CLASSIC 110 CY BLACK 0,6/1 kV**

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® CLASSIC 110 CY BLACK				
1121232	2 X 0.75	10.5	46	150
1121233	3 G 0.75	10.9	56	180
1121235	4 G 0.75	11.4	67	214
1121236	4 X 0.75	11.4	67	214
1121237	5 G 0.75	12.1	78	272
1121241	7 G 0.75	12.9	97	242
1121247	12 G 0.75	15.8	168	464
1121251	18 G 0.75	18	229	616
1121254	25 G 0.75	20.7	296	762
1121266	2 X 1.0	10.8	52	160
1121267	3 G 1.0	11.2	66	182
1121268	3 X 1.0	11.2	66	182
1121269	4 G 1.0	11.8	79	210
1121270	4 X 1.0	11.8	79	210
1121271	5 G 1.0	12.6	93	252
1121274	7 G 1.0	13.3	117	335
1121280	12 G 1.0	16.4	204	522
1121284	18 G 1.0	18.7	280	687
1121290	25 G 1.0	21.6	369	884
1121306	2 X 1.5	11.8	69	243
1121307	3 G 1.5	12.3	87	273
1121308	3 X 1.5	12.3	87	273
1121309	4 G 1.5	13	102	290
1121310	4 X 1.5	13	102	290
1121311	5 G 1.5	13.9	125	352
1121314	7 G 1.5	15	180	448
1121320	12 G 1.5	18.7	281	690
1121324	18 G 1.5	21.8	391	938
1121328	25 G 1.5	25.1	518	1180
1121340	3 G 2.5	13.5	123	315
1121342	4 G 2.5	14.6	168	349
1121344	5 G 2.5	15.7	204	515
1121346	7 G 2.5	17	265	619

Last Update (11.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16

**ÖLFLEX® CLASSIC 110 CY BLACK 0,6/1 kV**

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1121349	12 G 2.5	21.7	421	936
1121360	4 G 4.0	16.2	238	587
1121361	5 G 4.0	17.7	302	689
1121362	7 G 4.0	19	396	828
1121367	4 G 6.0	17.7	318	715
1121368	5 G 6.0	19.2	419	862
1121372	4 G 10.0	21.7	574	875
1121373	5 G 10.0	23	612	1037
1121377	4 G 16.0	24.3	809	1400
1121378	5 G 16.0	26.7	935	1600
1121381	4 G 25.0	29.8	1165	2179
1121385	4 G 35.0	32.7	1683	2893
1121388	4 G 50.0	39.6	2368	4094
1121391	4 G 70.0	44.5	3261	5467
1121394	4 G 95.0	51	4055	5849
1121397	4 G 120.0	58.1	5225	7509

Last Update (1.1.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet.  
PN 0456 / 02\_03\_16