

## ÖLFLEX® CLASSIC 110 BK

VDE-registered oil-resistant PVC control cable with black outer sheath for a wide range of applications

ÖLFLEX® CLASSIC 110 BK - PVC control cable, VDE registered, oil resistant, flexible and UV-resistant for various applications, 300/500V, also for YSLY or YY






### Info

CPR: Article number choice under [www.lappkabel.com/cpr](http://www.lappkabel.com/cpr)

With black outer sheath, UV-resistant

VDE certificate of conformity with  
factory surveillance



-  Good chemical resistance
-  Oil-resistant
-  Power chain
-  Torsion-resistant
-  UV-resistant

### Benefits

Suitable for outdoor applications

Wide choice of standardized lengths and individual cuts

### Application range

For fixed installation as well as occasional flexing at free, non-continuously recurring movement without tensile load

Dry or damp rooms that are subject to medium mechanical loads

Last Update (17.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## ÖLFLEX® CLASSIC 110 BK

Suitable for torsional applications which are typical for the loop in wind turbine generators (WTG)

In power chains for a travelling distance up to 5 m and 0,2 ... 1 million bending cycles, for following dimensions: 0,5 to 2.5mm<sup>2</sup> and 2 to 7 conductors

Suitable for outdoor applications

### Product features

Flame-retardant according IEC 60332-1-2

Good chemical resistance, see catalogue appendix T1

Oil-resistant according to DIN EN 50290-2-22 (TM54)

UV and weather-resistant according to ISO 4892-2

### Norm references / Approvals

VDE reg. no. 7030 for the following sizes:

up to 2.5 mm<sup>2</sup>: 2 - 65 cores

from 4 mm<sup>2</sup>: 2 - 7 cores

from 25 mm<sup>2</sup>: 2 - 5 cores

### Product Make-up

Fine-wire strand made of bare copper wires

PVC insulation LAPP P8/1

Cores twisted in layers

PVC outer sheath, black (RAL 9005)

### Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000104

ETIM 5.0 Class-Description: Control cable

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000104

ETIM 6.0 Class-Description: Control cable

Core identification code:

Black with white numbers acc. to VDE 0293-334

Conductor stranding:

Fine wire according to DIN EN 60228 (VDE 0295), class 5 / IEC 60228 class 5

Torsion movement in WTG:

TW-0 & TW-1, refer to Appendix T0

Minimum bending radius:

Occasional flexing: 10 x outer diameter

In power chains: 15 x outer diameter

Fixed installation: 4 x outer diameter

Nominal voltage:

U0/U: 300/500 V

Test voltage:

4000 V

Protective conductor:

G = with GN-YE protective conductor

X = without protective conductor

Temperature range:

Occasional flexing: -15 °C to +70 °C

In power chains: -5 °C to +70 °C

Fixed installation: -40 °C to +80 °C

### Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Last Update (17.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## ÖLFLEX® CLASSIC 110 BK

Packaging size: coil  $\leq$  30 kg or  $\leq$  250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

**ÖLFLEX® CLASSIC 110 BK**

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1119809	2 X 0.75	5.4	14.4	45
1119871	3 G 0.75	5.7	21.6	55
1119892	3 X 0.75	5.7	21.6	55
1119872	4 G 0.75	6.2	28.8	66
1119893	4 X 0.75	6.2	28.8	66
1119873	5 G 0.75	6.7	36	79
1119874	7 G 0.75	7.3	50.4	101
1119875	12 G 0.75	9.9	86.4	171
1119876	18 G 0.75	11.7	130	244
1119877	25 G 0.75	13.8	180	337
1119878	34 G 0.75	15.9	245	448
1119894	2 X 1.0	5.7	19.2	53
1119244	3 G 1.0	6	28.8	65
1119895	3 X 1.0	6	28.8	65
1119245	4 G 1.0	6.5	38.4	79
1119896	4 X 1.0	6.5	38.4	79
1119246	5 G 1.0	7.1	48	94
1119897	5 X 1.0	7.1	48	94
1119247	7 G 1.0	8	67.2	126
1119248	12 G 1.0	10.5	115	205
1119249	18 G 1.0	12.7	173	290
1119251	25 G 1.0	14.7	240	390
1119252	34 G 1.0	17.1	326	551
1119898	2 X 1.5	6.3	28.8	68
1119020	3 G 1.5	6.7	43.2	84
1119899	3 X 1.5	6.7	43.2	84
1119879	4 G 1.5	7.2	57.6	104
1119900	4 X 1.5	7.2	57.6	104
1119880	5 G 1.5	8.1	72	128
1119911	5 X 1.5	8.1	72	128
1119881	7 G 1.5	8.9	101	166
1119913	7 X 1.5	8.9	101	166
1119882	12 G 1.5	12	173	279
1119883	18 G 1.5	14.4	259	407

Last Update (17.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)You can find the current technical data in the corresponding data sheet:  
PN 0456 / 02\_03\_16



# ÖLFLEX® CLASSIC 110 BK

Article number	Number of cores and mm <sup>2</sup> per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
1119884	25 G 1.5	16.9	360	560
1119914	2 X 2.5	7.5	48	100
1119885	3 G 2.5	8.1	72	132
1119886	4 G 2.5	8.9	96	163
1119887	5 G 2.5	10	120	200
1119888	7 G 2.5	11.1	168	267
1119889	12 G 2.5	14.8	288	444
1119890	18 G 2.5	17.8	432	648
1119891	25 G 2.5	20.8	600	890
1119915	3 G 4.0	9.9	115.2	201
1119916	4 G 4.0	10.8	154	249
1119917	5 G 4.0	12.1	192	315
1119918	4 G 6.0	13	230	365
1119919	5 G 6.0	14.5	288	447
1119920	4 G 10.0	16.2	384	590
1119921	5 G 10.0	18.1	480	722
1119922	4 G 16.0	18.8	614	1087
1119923	5 G 16.0	21.2	768	1370

Last Update (17.12.2024)

©2024 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16