

EPIC® H-B 16 TG-RO

Housing design H-B. The industry standard.

The robust metal housing is ideal for use in the plastics industry. It has a direct cable entry and pivots for a single lever.

Info

Non-slip ridges for comfortable disconnecting
Protection rating UL50E tested



Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

The housing standard. Wide choice for all applications

Application range

Plant engineering
Light & sound technology
Plastics industry

Product features

Hood, low version

Last Update (11.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

EPIC® H-B 16 TG-RO

Reels for single lever
Straight cable entry
Versions with / without neck

Technical Data

Classification ETIM 5:

ETIM 5.0 Class-ID: EC000437

ETIM 5.0 Class-Description: Housing for industrial connectors

Classification ETIM 6:

ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

Material:

Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel

Sealing: NBR

Protection rating:

IP 65 (latched)

UL50 Type 12 (latched)

VDE-tested:

Certified production control: VDE-REG. no.: B437

UL-tested:

UL File Number: E75770

Temperature range:

-40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

EPIC® H-B 16 TG-RO

Article number	Article description	M	PG	Neck	Packaging unit
H-B housing: hood (straight cable entry, bolts for single lever)					
10080900	H-B 16 TG-RO 21	-	21	yes	5
19080900	H-B 16 TG-RO M25	25	-	-	5

Last Update (11.01.2026)

©2026 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16