


# EPIC® H-B 16 TS

Housing design H-B. The industry standard.

The robust metal housing for use in investment construction contains the pivots for a direct lever and a side cable entry.

## Info

Non-slip ridges for comfortable disconnecting Protection rating UL50E tested







Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

### **Benefits**

The housing standard. Wide choice for all applications

# **Application range**

Plant engineering Light & sound technology Plastics industry

# **Product features**

Hood, low version

Last Update (11.11.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02\_03.16



# EPIC® H-B 16 TS

Bolts for double lever Side cable entry Versions with neck

**Technical Data** 

Classification ETIM 5: ETIM 5.0 Class-ID: EC000437

ETIM 5.0 Class-Description: Housing for industrial connectors

Classification ETIM 6: ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

Material: Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel

Sealing: NBR

Protection rating: IP 65 (latched)

Protection rating UL50E tested

VDE-tested: Certified production control: VDE-REG. no.: B437

UL-tested:

UL File Number: E75770

Temperature range: -40°C to +100°C, short-term up to +125°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.



EPIC® H-B 16 TS

#### Article description М Packaging unit Article number H-B 16 TS M25 25 5 19082000 H-B 16 TS M32 32 5 19092000