

## ETHERLINE® ACCESS U

Industrial unmanaged Ethernet switches

Industrial network switches for ethernet based solutions in Smart Factories.

### Info

Redundant power inputs

Robust metal housing and DIN rail mounting



Supplementary automation components from Lapp



Mechanical and plant engineering

### Benefits

Improve your total cost of ownership with faster installation and lower downtime

Most flexible and globally present solutions from one hand

### Product features

RJ45 Ports: 10/100 BaseT(X)

RJ45 Ports: 10/100/1000 BaseT(X)

Packet Buffer Size: min. 1Mbit

Broadcast storm protection

Redundant Power Input: 24 VDC

### Norm references / Approvals

UL 61010

Shock IEC 60068-2-27

Freefall IEC60068-2-32

Vibration IEC 60068-2-6

### Technical Data

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03.16

## ETHERLINE® ACCESS U

Classification ETIM 5:	ETIM 5.0 Class-ID: EC000734 ETIM 5.0 Class-Description: Network switch
Classification ETIM 6:	ETIM 6.0 Class-ID: EC000734 ETIM 6.0 Class-Description: Network switch
power supply:	DC 24 V (18-30 V DC)
Protection rating:	IP 30
Temperature range:	-10°C to +60°C

### Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.  
Prices are net prices without VAT and surcharges. Sale to business customers only.



## ETHERLINE® ACCESS U

Article number	Article designation	Type	number of ports
Unmanged switches with RJ45			
21700123	ETHERLINE® ACCESS U05T-2GEN	Unmanaged	5 x RJ45
21700124	ETHERLINE® ACCESS U08T-2GEN	Unmanaged	8 x RJ45
21700120	ETHERLINE® ACCESS U16T	Unmanaged	16 x RJ45
Gigabit Unmanaged switches			
21700129	ETHERLINE® ACCESS U08GT	Unmanaged	8 x RJ45

Last Update (15.05.2025)

©2025 Lapp Group - Technical changes reserved

Product Management [www.lappkabel.de](http://www.lappkabel.de)

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02\_03\_16