

EPIC® H-B 24 TG-RO

Housing design H-B. The industry standard.

The robust metal housing with pivots for a single lever and a direct cable entry is not only ideal for use within the plastics industry.

Info

Non-slip ridges for comfortable disconnecting Protection rating UL50E tested







Supplementary automation components from Lapp



Mechanical and plant engineering



Mechanical resistance



Robust



Waterproof

Benefits

Ideal for many applications due to a wide range of housings and inserts

Application range

Plant engineering Light & sound technology Plastics industry

Product features

Hood, low version

Last Update (13.11.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16



EPIC® H-B 24 TG-RO

Reels for single lever Straight cable entry Versions with / without neck

Technical Data

Classification ETIM 5: ETIM 5.0 Class-ID: EC000437

ETIM 5.0 Class-Description: Housing for industrial connectors

Classification ETIM 6: ETIM 6.0 Class-ID: EC000437

ETIM 6.0 Class-Description: Housing for industrial connectors

Material: Housing: powder-coated aluminium alloy, grey

Lever: zinc-plated steel

Sealing: NBR

Protection rating: IP 65 (latched)

NEMA 250, UL50E: 12 (latched)

VDE-tested: Certified production control: VDE-REG. no.: B437

UL-tested:

UL File Number: E75770

Temperature range: -40°C to +100°C, short-term up to +125°C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.



EPIC® H-B 24 TG-RO

Article description М Packaging unit Article number H-B 24 TG-RO M25 25 5 19121900 H-B 24 TG-RO M32 32 5 19111900