ETHERLINE® ACCESS NF

Industrial NAT router with firewall function

Industrial network switches for ethernet based solutions in Smart Factories.

Info
compact design
Tailor-made solution





Supplementary automation components from Lapp

Mechanical and plant engineering

Benefits
compact design with high port density
reduced installation effort in existing networks
easy Configuration via web-interface
space saving and industrial grade DIN rail mounting

Application range
industrial networks

Product features
RJ45 Ports: 10/100 BaseT(X)
NAT (Basic NAT, NAPT) and port forwarding
integrated Firewall feature
Network Segmentation - IP ranges in NAT mode possible - from firmware V1.08.400

Norm references / Approvals
UL 61010

Last Update (17.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

ETHERLINE® ACCESS NF

Technical Data

power supply:	DC 24 V (18-30 V DC)
Protection rating:	IP20
Temperature range:	-40 °C up to +75 °C

Note

Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (17.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

ETHERLINE® ACCESS NF

Article number	Article designation	Type	number of ports	MTBF in years
21700141	ETHERLINE® ACCESS NF04T	Managed	4 x RJ45	>14.01

Last Update (17.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16