ETHERLINE® ACCESS UF

Industrial unmanaged Ethernet switches in compact design

Industrial network switches for ethernet based solutions in Smart Factories.

Info
compact design







Supplementary automation components from Lapp

Mechanical and plant engineering

Benefits
compact design with high port density
PROFINET®enabled device
space saving and industrial grade DIN rail mounting

Application range
industrial networks

Product features
Switches with 5, 8 and 16 ports
RJ45 Ports: 10/100 BaseT(X)

Norm references / Approvals
UL 61010

Technical Data

power supply:	DC 24 V (18-30 V DC)
Protection rating:	IP20

Last Update (17.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

ETHERLINE® ACCESS UF

Temperature range:	-25 °C to +60 °C

Note
Photographs and graphics are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

Last Update (17.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16

LAPP

PRODUCT INFORMATION

ETHERLINE® ACCESS UF

Article number	Article designation	Type	number of ports	MTBF in years
21700144	ETHERLINE® ACCESS UF05T	Unmanaged	5 x RJ45	>35.55
21700145	ETHERLINE® ACCESS UF08T	Unmanaged	8 x RJ45	>29.70
21700146	ETHERLINE® ACCESS UF16T	Unmanaged	16 x RJ45	>16.62

Last Update (17.05.2025)
©2025 Lapp Group - Technical changes reserved
Product Management www.lappkabel.de
You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16